

## RAPID START LAMPS

### High Output (800mA) Standard Rapid Start Lamps

Nominal Wattage	Bulb	Nominal Length (in)	MOL (in)	Base	Product Number	Ordering Abbreviation	Pkg Qty	Avg Rated Life @3hrs/start	CCT (K)	Approx Lumens		Symbols & Footnotes	
										Initial	Mean		
42	T12	30	27.91	Recessed DC	25322	F30T12/CW/HO	30	9000	4200	60	2250	1825	31,33,48
45	T12	36	33.91	Recessed DC	25333	F36T12/CW/HO	30	9000	4200	60	2850	2309	31,33,48
					25334	F36T12/DSGN50/HO	30	9000	5000	90	2100	1701	CRU 31,33,48
					25332	F36T12/D/HO	30	9000	6500	76	2500	2025	CRU 31,33,48
55	T12	42	39.91	Recessed DC	25342	F42T12/CW/HO	30	9000	4200	60	3400	2754	31,33,48
					25344	F42T12/DSGN50/HO	30	9000	5000	90	2550	2066	CRU 31,33,48
					25343	F42T12/D/HO	30	9000	6500	76	3050	2471	CRU 31,33,48
60	T12	48	46	Recessed DC	25147	F48T12/WW/HO	30	12000	3000	52	4130	3345	31,33,48,97
					25148	F48T12/D830/HO	30	12000	3000	80	4400	4048	CRU 31,33,48,97
					25154	F48T12/D35/HO	30	12000	3500	70	4250	3825	CRU 31,33,48,97
					25136	F48T12/D41/HO	30	12000	4100	70	4250	3443	CRU 31,33,48,97
					25146	F48T12/CW/HO	30	12000	4200	60	4050	3281	31,33,48,97
					25122	F48T12/CW/HO/ECO	30	12000	4200	60	4050	3281	31,33,48,76,97
					25153	F48T12/DSGN50/HO	30	12000	5000	90	3050	2471	CRU 31,33,48,97
					25150	F48T12/D/HO	30	12000	6500	76	3600	2916	CRU 31,33,48,97
75	T12	60	57.91	Recessed DC	25128	F60T12/D35/HO	30	12000	3500	70	5600	5040	CRU 31,33,48,97
					25126	F60T12/CW/HO	30	12000	4200	60	5200	4212	31,33,48,97
					25119	F60T12/DSGN50/HO	30	12000	5000	90	3850	3119	CRU 31,33,48,97
					25120	F60T12/D/HO	30	12000	6500	76	4600	3826	CRU 31,33,48,97
80	T12	64	61.91	Recessed DC	25352	F64T12/CW/HO	30	12000	4200	60	5750	4658	31,33,48,97
					25355	F64T12/DSGN50/HO	30	12000	5000	90	4200	3402	CRU 31,33,48,97
					25353	F64T12/D/HO	30	12000	6500	76	4900	3969	CRU 31,33,48,97
85	T12	72	69.91	Recessed DC	25098	F72T12/D830/HO	15	12000	3000	80	6750	6210	CRU 1,31,33,48,97
					25177	F72T12/WW/HO	15	12000	3000	52	6400	5184	1,31,33,48,97
					27249	F72T12/D35/HO	15	12000	3500	70	6650	5985	CRU 1,31,33,48,97
					25281	F72T12/D835/HO	15	12000	3500	80	6750	6210	CRU 1,31,33,48,97
					25182	F72T12/N/HO	15	12000	3600	86	4400	3564	CRU 1,31,33,48,97
					27245	F72T12/D41/HO	15	12000	4100	70	6650	5985	CRU 1,31,33,48,97
					25176	F72T12/CW/HO	15	12000	4200	60	6250	5063	1,31,33,48,97
					25171	F72T12/CW/HO/ECO	15	12000	4200	60	6250	5063	1,31,33,48,76
					25190	F72T12/DSGN50/HO	15	12000	5000	90	4600	3726	CRU 1,31,33,48,97
					25189	F72T12/D/HO	15	12000	6500	76	5550	4496	CRU 1,31,33,48,97
100	T12	84	81.91	Recessed DC	25384	F84T12/CW/HO	15	12000	4200	60	7550	6115	31,33,48,97
					25386	F84T12/DSGN50/HO	15	12000	5000	90	5600	4536	CRU 31,33,48,97
					25385	F84T12/D/HO	15	12000	6500	76	6700	5427	CRU 31,33,48,97
110	T12	96	93.91	Recessed DC	25149	F96T12/D30/HO	15	12000	3000	70	9050	8145	CRU 31,33,48,97
					25152	F96T12/D830/HO	15	12000	3000	80	9400	8648	CRU 31,33,48,97
					25165	F96T12/D35/HO	15	12000	3500	70	9050	8145	CRU 31,33,48,97
					25166	F96T12/D835/HO	15	12000	3500	80	9400	8648	CRU 31,33,48,97
					25162	F96T12/N/HO	15	12000	3600	86	6050	4900	CRU 31,33,48,97
					25184	F96T12/D41/HO	15	12000	4100	70	9050	8145	CRU 31,33,48,97