

OCTRON® AND OCTRON® CURVALUME® FLUORESCENT LAMPS**OCTRON® 700 Lamps**

Nominal Wattage	Bulb	Nominal Length (in)	MOL (in)	Base	Product Number	Ordering Abbreviation	Pkg Qty	Avg Rated Life @3hrs/start	CCT (K)	Approx Lumens		Symbols & Footnotes	
										Initial	Mean		
25	T8	36	35.78	Med Bipin	21941	F025/735/ECO	30	20000	3500	75	1950	1755	31,33,35,48, 52,76
					21942	F025/741/ECO	30	20000	4100	75	1950	1755	31,33,35,48, 52,76
40	T8	60	59.61	Med Bipin	22102	F040/730/ECO	30	20000	3000	75	3500	3150	31,33,35,48, 52,76
					22103	F040/735/ECO	30	20000	3500	75	3500	3150	31,33,35,48, 52,76
					22104	F040/741/ECO	30	20000	4100	75	3500	3150	31,33,35,48, 52,76

OCTRON® 800 XP® 8 Foot SUPERSAVER® Lamps

Nominal Wattage	Bulb	Nominal Length (in)	MOL (in)	Base	Product Number	Ordering Abbreviation	Pkg Qty	Avg Rated Life @3hrs/start	CCT (K)	Approx Lumens		Symbols & Footnotes	
										Initial	Mean		
55	T8	96	94	Single Pin	22100	F096/835/XP/SS/ECO	24	18000	3500	85	5700	5415	7,31,33,76, 85
					22101	F096/841/XP/SS/ECO	24	18000	4100	85	5700	5415	7,31,33,76, 85

OCTRON® 800 XP® 8 Foot Lamps

Nominal Wattage	Bulb	Nominal Length (in)	MOL (in)	Base	Product Number	Ordering Abbreviation	Pkg Qty	Avg Rated Life @3hrs/start	CCT (K)	Approx Lumens		Symbols & Footnotes	
										Initial	Mean		
59	T8	96	94	Single Pin	22036	F096/830/XP/ECO	24	18000	3000	85	6100	5795	31,33,44,48, 76,85
					22034	F096/835/XP/ECO	24	18000	3500	85	6100	5795	31,33,44,48, 76,85
					22032	F096/841/XP/ECO	24	18000	4100	85	6100	5795	31,33,44,48, 76,85
					22174	F096/850/XP/ECO	24	18000	5000	85	6100	5795	31,33,44,48, 76,85

OCTRON® 800 8 Foot Lamps

Nominal Wattage	Bulb	Nominal Length (in)	MOL (in)	Base	Product Number	Ordering Abbreviation	Pkg Qty	Avg Rated Life @3hrs/start	CCT (K)	Approx Lumens		Symbols & Footnotes	
										Initial	Mean		
59		96	94	Single Pin	22147	F096/830/ECO	24	15000	3000	82	5900	5428	10,31,33, 48,76
					22148	F096/835/ECO	24	15000	3500	82	5900	5428	10,31,33, 48,76
					22149	F096/841/ECO	24	15000	4100	82	5900	5428	10,31,33, 48,76
					22173	F096/850/ECO	24	15000	5000	80	5900	5428	10,31,33, 48,76
86	T8	96	93.91	Recessed DC	22206	F096/835/HO/ECO	24	18000	3500	85	8200	7710	31,33,48,76
					22207	F096/841/HO/ECO	24	18000	4100	85	8200	7710	31,33,48,76