

OCTRON® AND OCTRON® CURVALUME® FLUORESCENT LAMPS

OCTRON® 800 XP® Lamps

Nominal Wattage	Bulb	Nominal Length (in)	MOL (in)	Base	Product Number	Ordering Abbreviation	Pkg Qty	Avg Rated Life @3hrs/start	CCT (K)	Approx Lumens @25°C/77°F		Symbols & Footnotes	
										Initial	Mean		
25	T8	36	35.78	Med Bipin	22194	F025/850/XP/ECO	30	24000	5000	85	2175	2065	31,33,44,48, 52,76,87
					21719	F025/865/XP/ECO	30	24000	6500	85	2000	1900	31,33,44,48, 52,76,87
40	T8	60	59.61	Med Bipin	21912	F040/830/XP/ECO	30	24000	3000	85	3750	3560	31,33,44,48, 52,76,87
					21911	F040/835/XP/ECO	30	24000	3500	85	3750	3560	31,33,44,48, 52,76,87
					21916	F040/841/XP/ECO	30	24000	4100	85	3750	3560	31,33,44,48, 52,76,87
					21721	F040/865/XP/ECO	30	24000	6500	85	3650	3468	31,33,44,48, 52,76,87


OCTRON® 700 XP® Lamps

Nominal Wattage	Bulb	Nominal Length (in)	MOL (in)	Base	Product Number	Ordering Abbreviation	Pkg Qty	Avg Rated Life @3hrs/start (@12hrs/start)	CCT (K)	Approx Lumens @25°C/77°F		Symbols & Footnotes	
										Initial	Mean		
32	T8	48	47.78	Med Bipin	21711	F032/730/XP/ECO	30	36000 (42000)	3000	78	2850	2705	31,33,44, 48,52,76,94
					22044	F032/735/XP/ECO	30	36000 (42000)	3500	78	2850	2705	31,33,44, 48,52,76,94
					21712	F032/741/XP/ECO	30	36000 (42000)	4100	78	2850	2705	31,33,44, 48,52,76,94

Nominal Wattage	Bulb	Nominal Length (in)	MOL (in)	Base	Product Number	Ordering Abbreviation	Pkg Qty	Avg Rated Life @3hrs/start	CCT (K)	Approx Lumens @25°C/77°F		Symbols & Footnotes	
										Initial	Mean		
17	T8	24	23.78	Med Bipin	21699	F017/735/XP/ECO	30	24000	3500	78	1325	1255	31,33,44,48, 52,76,87
					21637	F017/741/XP/ECO	30	24000	4100	78	1325	1255	31,33,44,48, 52,76,87
25	T8	36	35.78	Med Bipin	21698	F025/735/XP/ECO	30	24000	3500	78	2050	1945	31,33,44,48, 52,76,87
					21639	F025/741/XP/ECO	30	24000	4100	78	2050	1945	31,33,44,48, 52,76,87

OCTRON® 800 Lamps


Nominal Wattage	Bulb	Nominal Length (in)	MOL (in)	Base	Product Number	Ordering Abbreviation	Pkg Qty	Avg Rated Life @3hrs/start (@12hrs/start)	CCT (K)	Approx Lumens @25°C/77°F		Symbols & Footnotes	
										Initial	Mean		
32	T8	48	47.78	Med Bipin	21777	F032/830/ECO	30	30000 (35000)	3000	85	2950	2802	21,31,33, 48,52,76,94
					21779	F032/835/ECO	30	30000 (35000)	3500	85	2950	2802	21,31,33, 48,52,76,94
					21781	F032/841/ECO	30	30000 (35000)	4100	85	2950	2802	21,31,33, 48,52,76,94
					22143	F032/850/ECO	30	30000 (35000)	5000	80	2800	2660	21,31,33, 48,52,76,94
17	T8	24	23.78	Med Bipin	22135	F017/830/ECO	30	20000	3000	82	1350	1240	31,33,35,48, 52,76



T8 U-Shaped 6"



T8 Med Bipin



T8 U-Shaped 1-5/8"

OCTRON® AND OCTRON® CURVALUME® FLUORESCENT LAMPS**OCTRON® 700 CURVALUME® U-SHAPED Lamps - 6" Leg Spacing**

Nominal Wattage	Bulb	Nominal Length (in)	MOL (in)	Base	Product Number	Ordering Abbreviation	Pkg Qty	Avg Rated Life @3hrs/start	CCT (K)	CRI	Approx Lumens		Symbols & Footnotes
											Initial	Mean	
32	T8	22.5	22.6	Med Bipin	22052	FB032/741/6/ECO	16	20000	4100	75	2750	2475	31,33,35,48,52,54,76
					22053	FB032/750/6/ECO	16	20000	5000	75	2625	2363	31,33,35,48,52,54,76

OCTRON® 5000K And 6500K for Displays, Signage and Backlighting

Nominal Wattage	Bulb	Nominal Length (in)	MOL (in)	Base	Product Number	Ordering Abbreviation	Pkg Qty	Avg Rated Life @3hrs/start	CCT (K)	CRI	Approx Lumens		Symbols & Footnotes
											Initial	Mean	
14	T8	18	17.91	Med Bipin	21731	F013/865XP/ECO	30	24000	6500	85	850	805	31,33,44,48,52,76,87
15	T8	20	19.78	Med Bipin	21868	F014/950/20in	30	20000	5000	90	750	638	31,33,35,48,52
					21716	F014/865/XP/ECO	30	24000	6500	85	1000	950	31,33,44,48,52,76,87
16	T8	10.5	10.60	Med Bipin	21726	F016/865XP	15	24000	6500	85	1125	1069	31,33,44,48,52,54,55,87
17	T8	24	23.78	Med Bipin	21871	F017/950/24in	30	20000	5000	90	800	680	31,33,35,48,52
					21718	F017/865/XP/ECO	30	24000	6500	85	1250	1188	31,33,44,48,52,76,87
21	T8	30	29.78	Med Bipin	21869	F021/950/30in	30	20000	5000	90	1000	850	31,33,35,48,52
					21730	F021/865/XP/ECO	30	24000	6500	85	1600	1520	31,33,44,48,52,76,87
25	T8	36	35.78	Med Bipin	21872	F025/950/36in	30	20000	5000	90	1250	1063	31,33,35,48,52
					21719	F025/865/XP/ECO	30	24000	6500	85	2000	1900	31,33,44,48,52,76,87
28	T8	40	39.78	Med Bipin	21870	F028/950/40in	30	20000	5000	90	1400	1190	31,33,35,48,52
32	T8	48	47.78	Med Bipin	21880	F032/950/48in	30	25000	5000	90	1800	1530	31,33,48,52
					21720	F032/865/XP/ECO	30	36000 ()	6500	85	2850	2708	20,31,33,48,52,76,94
40	T8	60	59.61	Med Bipin	21873	F040/950/60in	30	20000	5000	90	2200	1870	31,33,35,48,52
					21721	F040/865/XP/ECO	30	24000	6500	85	3650	3468	31,33,44,48,52,76,87

OCTRON® Specialty

Nominal Wattage	Bulb	Nominal Length (in)	MOL (in)	Base	Product Number	Ordering Abbreviation	Pkg Qty	Avg Rated Life @3hrs/start	CCT (K)	CRI	Approx Lumens		Symbols & Footnotes
											Initial	Mean	
32	T8	48	47.78	Med Bipin	21961	F032/GOLD	10	25000			1700	1530	31,33,35,43,48,52