

Product Number: 10117

Order Abbreviation: 40A15/IF/BL 120V

General Description: Incandescent A15 Bulb Shape Inside Frost Medium Aluminum Base 40Watt 120Volt Blister Pack 12Bulbs Per Case 1Bulb Per Package

Product Information	
Abbrev. With Packaging Info.	40A15IFBL 120V 12/CS 1/SKU
Approx. Lumens	410
Average Rated Life (hr)	1000
Base	Medium
Bulb	A15
Class	C (gas)
Color Rendering Index (CRI)	100
Color Temperature/CCT (K)	2850
Diameter (in)	1.875
Diameter (mm)	47.62
Filament	C-9
Lamp Finish	Inside Frost
Light Center Length - LCL (in)	2.375
Light Center Length - LCL (mm)	60
Maximum Overall Length - MOL (in)	3.500
Maximum Overall Length - MOL (mm)	88.9
Nominal Voltage (V)	120.00
Nominal Wattage (W)	40.00