

**Product Number:** 10298

**Order Abbreviation:** 25G16.5/BL 120V

**General Description:** Incandescent G16.5 Décor Clear Medium Aluminum Base 25Watt 120V Blister Pack 12Bulbs Per Case 2Bulbs Per Package

Product Information	
Abbrev. With Packaging Info.	25G165BL 120V 12/CS 2/SKU
Approx. Lumens	180
Average Rated Life (hr)	1500
Base	Medium
Bulb	G16.5
Class	C (gas)
Color Rendering Index (CRI)	100
Color Temperature/CCT (K)	2850
Diameter (in)	2.063
Diameter (mm)	52.39
Filament	C-7A
Lamp Finish	Clear
Maximum Overall Length - MOL (in)	3.000
Maximum Overall Length - MOL (mm)	76.2
Nominal Voltage (V)	120.00
Nominal Wattage (W)	25.00