

**Product Number:** 11428

**Order Abbreviation:** 50A 277V

**General Description:** Incandescent A19 Bulb Shape Inside Frost Finish Medium Aluminum Base 50Watt 277Volt

Product Information	
Abbrev. With Packaging Info.	50A277V 277V 120/CS 6/SKU
Approx. Lumens	475
Average Rated Life (hr)	1000
Base	Medium
Bulb	A19
Class	B (vacuum)
Color Rendering Index (CRI)	100
Color Temperature/CCT (K)	2850
Diameter (in)	2.375
Diameter (mm)	60.33
Filament	CC-7A
Lamp Finish	Inside Frost
Light Center Length - LCL (in)	2.500
Light Center Length - LCL (mm)	64
Maximum Overall Length - MOL (in)	4.438
Maximum Overall Length - MOL (mm)	112.7125
Nominal Voltage (V)	277.00
Nominal Wattage (W)	50.00