



S14



B15d



E14



S11



A21, A23



PS25



PAR 46, 64

**INCANDESCENT****SINGLE END**

ANSI Code	Ordering Abbreviation	Product Number	Watts (W)	Volts (V)	Lumens (lm)	Color Temp (K)	Avg Rated Life (hrs)	Base	Bulb	Pkg Qty	Symbols & Footnotes
	8013	76311	10	6			200	BA15D		100	46
	8017	76313	15	6			1000	B15D		100	
	8018	76314	15	6			100	B15D		100	46
	70314 (390153)	76304	25	6				P47D		100	
	70313 (390158)	76305	30	6				P47D	P35	100	
	8100	76321	30	5			600	E14		100	45
	111A	11624	75	120	1120	2900	15	SC Bayonet	S11	24	
	140	11625	75	120	1150	2900	35	Medium	S14	24	
	211 118V	11657	75	120	1215	3200	200	Medium	A21	12	
	212 118V	11656	150	120	2700	3050	200	Medium	A21	12	
BBA	BBA 118V	11619	250	120	8700	3400	4	Medium	A21	12	
BCA	BCA 118V	11655	250	120	8912	4800	12	Medium	A21	12	
ECA	ECA 120V	13365	250	120	6500		20	Medium Brass	A23	24	
EBV	EBV 118V	11558	500	120	17800	3400	8	Medium	PS25	24	
ECT	ECT 120V	11560	500	120	13650	3200	60	Medium	PS25	24	
	70335 BULK	76302		6				Special		200	

**PAR**

Product Number	Ordering Abbreviation	Watts (W)	Volts (V)	Base	Centerbeam Candlepower (cp)	Avg Rated Life (hrs)	Bulb	Pkg Qty	Symbols & Footnotes
15399	4551	250	28	G53	75000	25	PAR46	12	29
14988	4557	1000	28	G53	540000	50	PAR64	6	
14936	4559	600	28	G53	600000	100	PAR64	6	29
14994	5557	1000	28	G53	540000	50	PAR64	6	29,53

For the current listing of available products and more complete product information, please visit us at [www.sylvania.com](http://www.sylvania.com)