



Product Number: 11710

Order Abbreviation: 25A19/TB/RP 125V

General Description: Incandescent A19 Bulb Shape Transparent Blue Finish Medium Brass Base 25Watt 125Volt Retail Pack 6Bulbs Per Case 1Bulb Per Package

Product Information	
Abbrev. With Packaging Info.	25A19TBRP 125V 6/CS 1/SKU
Approx. Lumens	180
Average Rated Life (hr)	3000
Base	Medium Brass
Bulb	A19
Class	B (vacuum)
Color Rendering Index (CRI)	100
Color Temperature/CCT (K)	2850
Diameter (in)	2.375
Diameter (mm)	60.33
Filament	C-9
Lamp Finish	Blue
Light Center Length - LCL (in)	2.500
Light Center Length - LCL (mm)	64
Maximum Overall Length - MOL (in)	3.938
Maximum Overall Length - MOL (mm)	100.0125
Nominal Voltage (V)	125.00
Nominal Wattage (W)	25.00