



Energy Used Nominal Watts	Bulb	Base	Vendor ID NO. DCI 046135 UPC 46135 Item No.	Ordering Abbreviation Except Volts	Volts	Pkg. Qty.	Description	Class and Fil.	Life Avg. Rated Hours	Light Output Approx. Lmns. CBCP & Beam Spread	L.C.L.	M.O.L.
60	A-17	Med.	17765	60A17/99/XL ☐	130	120	Inside Frost, Excel Line®	C, CC-8	2500	775	3%	4%
<b>WE SUGGEST 60A17/52/SSXL 130 Volts, An Energy Saving Product</b>												
<i>[@ 120 volts, approximate 53 watts, 575 lumens, 6250 hours]<sup>33</sup></i>												
A-19	Med.	10640	60A		24	120	Inside Frost, Dental Spot	C, C-9	1000			4%
		11214	60A/RP		120	24	•Inside Frost	C, CC-8	1000	890	3%	4%
		10576	60A/SPK		115-125	24	•Soft Pink	C, CC-8	1000			4%
		12280	60A/GRO		120	6	Spot-GRO	C, C-9	1000			4%
		10553	60A/CL		120	120	•Clear	C, CC-8	1000	890	3%	4%
		11224	60A/CL/RP		120	24	•Clear	C, CC-8	1000	890	3%	4%
		10555	60A/CL		130	120	•Clear	C, CC-8	1000	890	3%	4%
<i>[@ 120 volts, approximate 53 watts, 660 lumens, 2500 hours]<sup>33</sup></i>												
		10480	60A/D		115-125	120	•Inside Frost, Daylight	C, CC-8	1000		3%	4%
		10479	60A/D		130	120	•Inside Frost, Daylight	C, CC-8	1000		3%	4%
		10613	60A/SB		120	120	•I.F., Silver Bowl <sup>7</sup>	C, CC-8	1000	758		4%
		11227	60A/W/DLSW/RP/2PK		120	24	•Double Life™ Soft White	C, CC-8	2000	800		4%
		11204	60A/W/DLSW/RP/4PK		120	48	•Double Life™ Soft White	C, CC-8	2000	800		4%
		11208	60A/W/RP		120	24	•Soft White	C, CC-8	1000	870		4%
<b>WE SUGGEST 60A17/52/W/ES/2PK or 4PK, An Energy Saving Product</b>												
		11205	60A/W/RP/4		120	48	•Soft White	C, CC-8	1000	870		4%
		11209	60A/W/RP		125	24	•Soft White	C, CC-8	1000	850		4%
<i>[@ 120 volts, approximate 56 watts, 725 lumens, 1500 hours]<sup>33</sup></i>												
		10390	60A/Y/RP		120	24	•Yellow Bug Light	C, CC-8	1000			4%
		10386	60A/Y/RP		130	24	•Yellow Bug Light	C, CC-8	1000			4%
		12416	60A/RS		120	120	•Inside Frost, Rough Service	C, C-17	1000	555	3%	4%
		12417	60A/RS		130	120	•Inside Frost, Rough Service	C, C-17	1000	555	3%	4%
<i>[@ 120 volts, approximate 53 watts, 410 lumens, 2500 hours]<sup>33</sup></i>												
		12418	60A/CL/RS		120	120	•Clear, Rough Service	C, C-17	1000	555	3%	4%
		10501	60A/SL		120	120	Safeline, Inside Frost	C, CC-8	1000		3%	4%
		10502	60A/SL/RP		120	12	Safeline, Inside Frost	C, CC-8	1000		3%	4%
		12288	60A19/CB		120	120	•Blue Ceramic	C, C-9	1000			4%
		12289	60A19/CG		120	120	•Green Ceramic	C, C-9	1000			4%
		12285	60A19/CR		120	120	•Red Ceramic	C, C-9	1000			4%
MB-19	Med.	18960	60A/HAL		120	12	Inside Frost, Tungsten Halogen Capsylite®	C, CC-8	3000	960	3%	4%
A-21	▼Med.	12458	60A21/TS		120	24	•Clear, Traffic Signal	C, C-9	2000	685	2%	4%
60	PAR-16	Med.	59030	60PAR16/CAP/NFL/30	120	15	Designer16®	C, CC-8	2000	1300 <sup>CP(30°)</sup>		2%
			59031	60PAR16/HAL/NFL/30		6	Narrow Flood <sup>26</sup>					
			59038	60PAR16/CAP/NFL/30	130	15	Designer 16®	C, CC-8	2000	1300 <sup>CP(30°)</sup>		2%
<i>[@ 120 volts, approximate 48 watts, 4000 hours]<sup>33</sup></i>												
			59032	60PAR16/CAP/NSP/10	120	15	Designer 16®	C, CC-8	2000	5000 <sup>CP(10°)</sup>		2%
							Narrow Spot <sup>26</sup>					
			59040	60PAR16/CAP/NSP/10	130	15	Designer 16®	C, CC-8	2000	5000 <sup>CP(10°)</sup>		2%
<i>[@ 120 volts, approximate 48 watts, 4000 hours]<sup>33</sup></i>												
							Narrow Spot <sup>26</sup>					

☐ means this bulb meets Federal minimum efficiency standards.

☐ Energy Saving Product/Value Added Product

● New Item

Footnotes/Symbols pages 162-164