

Product Number: 12572

Order Abbreviation: 67A21/40/8M 130V

General Description: Incandescent A21 Bulb Shape Traffic Signal Clear Medium Brass Base 67Watt 130Volt

Product Information	
Abbrev. With Packaging Info.	67A21408M 130V 24/CS 1/SKU
Approx. Lumens	610
Average Rated Life (hr)	8000
Base	Medium Brass
Bulb	A21
Class	C (gas)
Color Rendering Index (CRI)	100
Color Temperature/CCT (K)	2850
Diameter (in)	2.625
Diameter (mm)	66.68
Filament	C-9
Lamp Finish	Clear
Light Center Length - LCL (in)	2.438
Light Center Length - LCL (mm)	62
Maximum Overall Length - MOL (in)	4.438
Maximum Overall Length - MOL (mm)	112.7125
Nominal Voltage (V)	130.00
Nominal Wattage (W)	67.00