

Product Number: 12977

Order Abbreviation: 60A/RS/RP/1 120V

General Description: Incandescent A19 Bulb Shape Rough Service Inside Frost Finish Medium Aluminum Base 60Watt 120Volt Retail Pack 12Bulbs Per Case 1Bulb Per Package

Product Information	
Abbrev. With Packaging Info.	60ARSRP1 120V 12/CS 1/SKU
Approx. Lumens	555
Average Rated Life (hr)	1000
Base	Medium
Bulb	A19
Class	C (gas)
Color Rendering Index (CRI)	100
Color Temperature/CCT (K)	2850
Diameter (in)	2.375
Diameter (mm)	60.33
Family Brand Name	ROUGH SERVICE
Filament	C-9
Lamp Finish	Inside Frost
Light Center Length - LCL (in)	2.875
Light Center Length - LCL (mm)	73
Maximum Overall Length - MOL (in)	4.438
Maximum Overall Length - MOL (mm)	112.7125
Nominal Voltage (V)	120.00
Nominal Wattage (W)	60.00