



**Product Number:** 13103

**Order Abbreviation:** 200A21/W/1RP 120V

**General Description:** Incandescent A21 Bulb Shape Soft White Finish Medium Aluminum Base 200W 120V Retail Pack 12Bulbs Per Case 1Bulb Per Package

Product Information	
Abbrev. With Packaging Info.	200A21W1RP 120V 12/CS 1/SKU
Approx. Lumens	3650
Average Rated Life (hr)	750
Base	Medium
Bulb	A21
Class	C (gas)
Color Rendering Index (CRI)	100
Color Temperature/CCT (K)	2850
Diameter (in)	2.625
Diameter (mm)	66.68
Filament	CC-8
Lamp Finish	Soft White
Light Center Length - LCL (in)	3.875
Light Center Length - LCL (mm)	98
Maximum Overall Length - MOL (in)	5.313
Maximum Overall Length - MOL (mm)	134.9375
Nominal Voltage (V)	120.00
Nominal Wattage (W)	200.00