



Product Number: 13404

Order Abbreviation: 100A21 230V

General Description: Incandescent A21 Bulb Shape Inside Frost Finish Medium Aluminum Base 100Watt 230Volt

Product Information	
Abbrev. With Packaging Info.	100A21230V 230V 24/CS 6/SKU
Approx. Lumens	1260
Average Rated Life (hr)	1000
Base	Medium
Bulb	A21
Class	C (gas)
Color Rendering Index (CRI)	100
Color Temperature/CCT (K)	2850
Diameter (in)	2.625
Diameter (mm)	66.68
Filament	C-9
Lamp Finish	Inside Frost
Light Center Length - LCL (in)	3.875
Light Center Length - LCL (mm)	98
Maximum Overall Length - MOL (in)	5.313
Maximum Overall Length - MOL (mm)	134.9375
Nominal Voltage (V)	230.00
Nominal Wattage (W)	100.00