

Product Number: 13678

Order Abbreviation: 25B10C/T/BL/2PK 120V

General Description: Incandescent B10 Décor Bulb Shape Torpedo Tip Clear Finish Candelabra Base 25Watt 120Volt Blister Pack 12Bulbs Per Case 2Bulbs Per Package

Product Information	
Abbrev. With Packaging Info.	25B10CTBL2PK 120V 12/CS 2/SKU
Average Rated Life (hr)	1500
Base	Candelabra
Bulb	B10
Class	C (gas)
Color Rendering Index (CRI)	100
Color Temperature/CCT (K)	2850
Diameter (in)	1.250
Diameter (mm)	31.75
Filament	C-7A
Lamp Finish	Clear
Maximum Overall Length - MOL (in)	3.625
Maximum Overall Length - MOL (mm)	92.075
Nominal Voltage (V)	120.00
Nominal Wattage (W)	25.00