



B13



F10



F15 Med



G16.5

**Incandescent B13 Fan Lamps**

Nominal Wattage	MOL (in)	Base	Product Number	Ordering Abbreviation	Voltage	Pkg Qty	Finish	Average Rated Life (hrs)	CCT (K)	CRI	Lumens	Filament	Notes
40	4.63	Medium	13367	40B13/FAN/BL/2PK 120V	120	12	Clear	1500	2850	100	455	C-9	▲●●,13,14
			13369	40B13/DL/FAN/BL/2PK 120V	120	12	Clear	3000	2850	100	455	C-9	▲●●,13,14
			13785	40B13/CRYSTAL/FAN/BL/2PK 120V	120	12	Crystal	1500	2850	100	455	C-9	▲●●,13,14
40	4.00	Candelabra	13357	40B13C/CL/FAN/2/12/BL 120V	120	12	Clear	1500	2850	100	360	C-9	▲●●,13,14
60	4.63	Medium	13368	60B13/FAN/BL/2PK 120V	120	12	Clear	1500	2850	100	650	C-9	▲●●,13,14
			13370	60B13/DL/FAN/BL/2PK 120V	120	12	Clear	3000	2850	100	650	C-9	▲●●,13,14
60	4.00	Candelabra	13263	60B13C/CL/FAN/2/12/BL 120V	120	12	Clear	1500	2850	100	650	C-9	▲●●,13,14

**Incandescent F10 and F15 Flame Lamps**

Nominal Wattage	MOL (in)	Base	Product Number	Ordering Abbreviation	Voltage	Pkg Qty	Finish	Average Rated Life (hrs)	CCT (K)	CRI	Lumens	Filament	Notes
15	3.06	Candelabra	13434	15FC/NC/BL/2PK 120V	120	12	Iridescent	1500	2850	100	90	C-7A	▲●●,1,4
15	4.50	Candelabra	13823	25F/AC/BL/2PK 120V	120	12	Amber Iridescent	1500	2850	100	-	C-7A	▲●●,1,4
			13821	25F/AC/BL/2PK 120V	120	12	Iridescent	1500	2850	100	205	C-7A	▲●●,1,4
			13820	25F/W/BL/2PK 120V	120	12	Soft White	1500	2850	100	170	C-7A	▲●●,1,4
			13986	40F/AC/BL/2PK 120V	120	12	Amber	1500	2850	100	335	C-7A	▲●●,1,4
40	4.50	Medium	13974	40F/CL 120V	120	24	Clear	1500	2850	100	340	C-7A	▲●●,1,4
			13985	40F/AC/BL/2PK 120V	120	12	Iridescent	1500	2850	100	335	C-7A	▲●●,1,4
			13984	40F/W/BL/2PK 120V	120	12	White	1500	2850	100	325	C-7A	▲●●,1,4
60	4.50	Medium	13992	60F/BL 120V	120	12	Clear	1500	2850	100	690	C-7A	▲●●,1,4
			13993	60F/CL 120V	120	24	Clear	1500	2850	100	690	C-7A	▲●●,1,4
			13982	60F/AC/BL/2PK 120V	120	12	Iridescent	1500	2850	100	590	C-7A	▲●●,1,4
			13982	60F/AC/BL/2PK 120V	120	12	Iridescent	1500	2850	100	590	C-7A	▲●●,1,4

**Incandescent Globe Lamps****Incandescent G16.5 Globe**

Nominal Wattage	MOL (in)	Base	Product Number	Ordering Abbreviation	Voltage	Pkg Qty	Finish	Average Rated Life (hrs)	CCT (K)	CRI	Lumens	Filament	Notes
15	3.00	Candelabra	13616	15G16.5C 120V	120	24	Clear	1500	2850	100	110	C-7A	●●●,1,4
			13709	15G16.5C/4M 120V	120	24	Clear	4000	2850	100	90	C-7A	●●●,1,4
25	3.00	Candelabra	13704	25G16.5C/4M 120V	120	24	Clear	4000	2850	100	170	C-7A	●●●,1,4
25	3.00	Medium	10298	25G16.5/BL 120V	120	12	Clear	1500	2850	100	180	C-7A	●●●,1,4
25	3.00	Candelabra	13618	25G16.5C 120V	120	24	Clear	1500	2850	100	180	C-7A	●●●,1,4
			13625	25G16.5C/BL 120V	120	12	Clear	1500	2850	100	180	C-7A	●●●,1,4
25	3.00	Medium	10297	25G16.5/W/BL 120V	120	12	Soft White	1500	2850	100	165	C-7A	●●●,1,4
25	3.00	Candelabra	13622	25G16.5C/W/BL 120V	120	12	Soft White	1500	2850	100	165	C-7A	●●●,1,4
40	3.00	Medium	10300	40G16.5/BL 120V	120	12	Clear	1500	2850	100	330	C-7A	●●●,1,4
40	3.00	Candelabra	13666	40G16.5C/BL 120V	120	12	Clear	1500	2850	100	330	C-7A	●●●,1,4
			13702	40G16.5C 120V	120	24	Clear	1500	2850	100	330	C-7A	●●●,1,4
			10367	40G16.5C/DAY/2PK/BL 120V	120	12	Daylight	1500	2850	100	260	C-7A	●●●,1,4
40	3.00	Medium	10299	40G16.5/W/BL 120V	120	12	Soft White	1500	2850	100	280	C-7A	●●●,1,4
40	3.00	Candelabra	13667	40G16.5C/W/BL 120V	120	12	Soft White	1500	2850	100	280	C-7A	●●●,1,4
60	3.00	Medium	10302	60G16.5/BL 120V	120	12	Clear	1500	2850	100	560	C-7A	▼●●
			10301	60G16.5/W/BL/2PK 120V	120	12	Soft White	1500	2850	100	550	C-7A	▼●●
60	3.00	Candelabra	13664	60G16.5C/W/BL 120V	120	12	Soft White	1500	2850	100	550	C-2	▼●●
			13665	60G16.5C/BL 120V	120	12	Clear	1500	2850	100	560	C-2	▼●●

Specifications subject to change without notice.

Notes on page 53