



Product Number: 13821

Order Abbreviation: 25F/IC/BL/2PK 120V

General Description: Incandescent F15 Décor Bulb Shape Iridescent Clear Finish Medium Aluminum Base 25Watt 120Volt 12Bulbs Per Case 2Bulbs Per Package

Product Information	
Abbrev. With Packaging Info.	25FICBL2PK 120V 12/CS 2/SKU
Approx. Lumens	205
Average Rated Life (hr)	1500
Base	Medium
Bulb	F15
Class	C (gas)
Color Rendering Index (CRI)	100
Color Temperature/CCT (K)	2850
Diameter (in)	1.875
Diameter (mm)	47.63
Filament	C-7A
Lamp Finish	Iridescent
Maximum Overall Length - MOL (in)	4.500
Maximum Overall Length - MOL (mm)	114.3
Nominal Voltage (V)	120.00
Nominal Wattage (W)	25.00