



BR30



PAR38 Med Skrt

INCANDESCENT

DIRECTIONAL INCANDESCENT LAMPS (cont.)

Incandescent BR30, BR40 and PAR38 Heat Lamps Reflector Lamps

Incandescent BR30 Reflector Lamps

Nominal Wattage	MOL (in)	Base	Product Number	Ordering Abbreviation	Voltage	Pkg Qty	Finish	Average Rated Life (hrs)	CCT (K)	CRI	Lumens	Filament	Notes
45	4.38	Medium	15103	45BR30/FL/RP 120V	120	6	Reflector	2000	2850	100	350	CC-6	●,1,3
65	5.38	Medium	10211	65BR30/OBLUE/IC 120V	120	12	Blue Reflector	2000	2850	100	350	CC-6	●,1,3
			10212	65BR30/OPINK/IC 120V	120	12	Pink Reflector	2000	2850	100	350	CC-6	●,1,3
			15148	65BR30/TRAY 120V	120	48	Reflector	2000	2850	100	600	CC-6	●,1,3
			15153	65BR30/PK/RP 120V	120	6	Pink Reflector	2000	2850	100	350	CC-6	●,1,3
			15149	65BR30/SP/RP 120V	120	6	Reflector	2000	2850	100	350	CC-6	●,1,3
			15160	65BR30/FL/RP 120V	120	6	Reflector	2000	2850	100	600	CC-6	●,1,3
			15165	65BR30/FL 120V	120	24	Reflector	2000	2850	100	600	CC-6	●,1,3
			15177	65BR30/DL/FL/RP 120V	120	6	Reflector	4000	2850	100	485	CC-6	●,1,3
			15223	65BR30/DAY/1/6/RP 120V	120	6	Reflector	2000	2850	100	420	CC-6	●,1,3
			15234	65BR30/FL/3/24 120V	120	24	Reflector	2000	2850	100	600	CC-6	●,1,3
			15246	65BR30/2/24/RP 120V	120	24	Reflector	2000	2850	100	600	CC-6	●,1,3
			13129	65BR30/FL 130V	130	24	Reflector	2000	2900	100	540	CC-6	●,1,3
			15167	65BR30/FL/SL/RP 130V	130	6	Reflector	2000	2850	100	530	CC-6	●,1,3
15172	65BR30/FL/CVP 130V	130	6	Reflector	2000	2850	100	540	CC-6	●,1,3			
65	6.50	Medium	15487	65BR/FL/DAY/1/6/RP 120V	120	6	Reflector	2000	2900	100	480	CC-6	●,1,3,4
65	6.50	Medium Brass	15332	65BR/DL/FL/RP 120V	120	6	Reflector	4000	2850	100	510	CC-6	1,3,4
65	6.50	Medium	15678	65BR/FL/RP 120V	120	6	Reflector	2000	2850	100	580	CC-6	●,1,3,4
			15292	65BR/FL 130V	130	24	Reflector	2000	2850	100	540	CC-6	●,1,3,4
			15679	65BR/CVP 130V	130	6	Reflector	2000	2850	100	540	CC-6	●,1,3,4
120	6.50	Medium	15836	120BRV/GROW/3/RP 120V	120	3	Reflector	2000	2850	100	-	CC-6	●,1,3,4
125	6.50	Medium	15451	125BR40HEAT/24PK 120V	120	24	Reflector	4000	-	-	-	C-9	●,1,3,4
250	6.50	Medium Brass	14664	250BR40/1 120V	120	6	Reflector	5000	2850	100	2000	CC-6	1,3,4
300	6.50	Medium Brass	14779	300BR/FL 120V	120	24	Reflector	2000	2850	100	3030	CC-2V	1,3,4

Incandescent PAR38 Heat Lamps

Nominal Wattage	MOL (in)	Base	Product Number	Ordering Abbreviation	Voltage	Pkg Qty	Finish	Average Rated Life (hrs)	CCT (K)	CRI	Lumens	Filament	Notes
100	4.44	Medium Skirted	13849	100PAR38/HEAT/RED 120V	120	15	Red	5000	2850	-	-	-	●,1,2
175	5.31	Medium Skirted	13836	175PAR38/HEAT/CL 120V	120	15	Clear	5000	2850	100	-	CC-6	●,1,2

For the current listing of available products and more complete product information, please visit us at www.sylvania.com.