



Product Number: 14150

Order Abbreviation: 60G25/DLSW/RP 120V

General Description: Incandescent G25 Décor Bulb Shape Double Life Soft White Finish Medium Aluminum Base 60Watt 120Volt Retail Pack 6Bulbs Per Case 1Bulb Per Package

Product Information	
Abbrev. With Packaging Info.	60G25DLSWRP 120V 6/CS 1/SKU
Approx. Lumens	460
Average Rated Life (hr)	3000
Base	Medium
Bulb	G25
Class	C (gas)
Color Rendering Index (CRI)	100
Color Temperature/CCT (K)	2850
Diameter (in)	3.125
Diameter (mm)	79.38
Family Brand Name	Double Life Soft White
Filament	C-9
Lamp Finish	Soft White
Maximum Overall Length - MOL (in)	4.438
Maximum Overall Length - MOL (mm)	112.7125
Nominal Voltage (V)	120.00
Nominal Wattage (W)	60.00