



Product Number: 14506

Order Abbreviation: 35PAR20/HAL/WFL40 120V

General Description: Tungsten Halogen CAPSYLITE PAR20 Reflector Lamp Medium Base 35Watt 120Volt Wide Flood Beam

| Product Information | |
|-----------------------------------|----------------------------------|
| Abbrev. With Packaging Info. | 35PAR20HALWFL40 120V 15/CS 1/SKU |
| Approx. Lumens | 360 |
| Average Rated Life (hr) | 2500 |
| Base | E26 Medium |
| Beam Angle (deg) | 40 |
| Beam Type | WFL |
| Bulb | PAR20 |
| Centerbeam Candlepower (cp) | 500 |
| Class | C (gas) |
| Color Rendering Index (CRI) | 100 |
| Color Temperature/CCT (K) | 2775 |
| Diameter (in) | 2.500 |
| Diameter (mm) | 63.50 |
| Ecologic | YES |
| Family Brand Name | CAPSYLITE® PAR20 |
| Filament | CC-8 |
| Horizontal Beam Angle (deg) | 40 |
| Lamp Finish | Reflector |
| Maximum Overall Length - MOL (in) | 3.250 |
| Maximum Overall Length - MOL (mm) | 79.375 |
| Nominal Voltage (V) | 120.00 |
| Nominal Wattage (W) | 35.00 |
| Vertical Beam Angle (deg) | 40 |