



Product Number: 14619

Order Abbreviation: 40G40/RP 120V

General Description: Incandescent G40 Décor Bulb Shape Clear Finish Medium Aluminum Base 40Watt 120V Retail Pack 6Bulbs Per Case 1Bulb Per Package

Product Information	
Abbrev. With Packaging Info.	40G40RP 120V 6/CS 1/SKU
Approx. Lumens	350
Average Rated Life (hr)	2500
Base	Medium
Bulb	G40
Class	C (gas)
Color Rendering Index (CRI)	100
Color Temperature/CCT (K)	2850
Diameter (in)	5.000
Diameter (mm)	127.00
Filament	C-9
Lamp Finish	Clear
Maximum Overall Length - MOL (in)	6.938
Maximum Overall Length - MOL (mm)	176.2125
Nominal Voltage (V)	120.00
Nominal Wattage (W)	40.00