



A19 Med



A21 Med

### GENERAL PURPOSE INCANDESCENT LAMPS

#### Incandescent A-Line Lamps for General Illumination, Task and Accent Lighting

#### General Purpose Incandescent A-Line Lamps

Nominal Wattage	MOL (in)	Base	Product Number	Ordering Abbreviation	Voltage	Pkg Qty	Finish	Average Rated Life (hrs)	CCT (K)	CRI	Lumens	Filament	Notes
25	3.94	Medium	10562	25A/W/RP 120V	120	24	Soft White	2500	2850	100	160	C-9	●, ●
			10634	25A/RP 120V	120	24	Inside Frost	2500	2850	100	190	C-9	●, ●
			10644	25A 120V	120	120	Inside Frost	2500	2850	100	190	C-9	●, ●
			10645	25A 130V	130	120	Inside Frost	2500	2850	100	180	C-9	●, ●
25	3.94	Medium Brass	10694	25A/CL 130V	130	120	Clear	2500	2850	100	180	C-9	●
50	4.44	Medium	11428	50A 277V	277	120	Inside Frost	1000	2850	100	475	CC-7A	●, ●
75	5.31	Medium Brass	11566	75A21 12V	12	24	Inside Frost	1000	2850	100	1420	C-6	●
100	5.31	Medium	13404	100A21 230V	230	24	Inside Frost	1000	2850	100	1260	C-9	●, ●
			13406	100A21 250V	250	24	Inside Frost	1000	2850	100	1230	C-9	●, ●
			13397	100A21 277V	277	24	Inside Frost	1000	2850	100	1040	C-7A	●, ●
150	5.31	Medium	13101	150A21/W/RP 120V	120	12	Soft White	750	2850	100	2640	CC-8	●, ●
			13125	150A21/CL/RP 120V	120	12	Clear	750	2850	100	2740	CC-8	●, ●
			13148	150A21/CL 130V	130	48	Clear	750	2850	100	2730	CC-8	●, ●
150	6.06	Medium	13041	150A23 120V	120	48	Inside Frost	750	2850	100	2810	CC-8	●, ●
200	5.31	Medium	13103	200A21/W/RP 120V	120	12	Soft White	750	2850	100	3650	CC-8	●, ●
			15476	200A21/CL/RP 120V	120	12	Clear	750	2850	100	3880	CC-8	●, ●
			15491	200A21/CL 130V	130	48	Clear	750	2850	100	3880	CC-8	●, ●
200	5.31	Medium Brass	15555	200A21/99/XL 125V	125	48	Standard Frost	2500	2850	100	2910	CC-8	●
200	5.31	Medium	15543	200A21 130V	130	48	Standard Frost	750	2850	100	3760	CC-8	●, ●

#### 3-WAY Incandescent Lamps

Nominal Wattage	MOL (in)	Base	Product Number	Ordering Abbreviation	Voltage	Pkg Qty	Finish	Average Rated Life (hrs)	CCT (K)	CRI	Lumens	Filament	Notes
15 135 150	5.31	3CONTACT Medium Aluminum	18009	15/150A/SECURITYLIGHT 120V	120	12	Soft White	1200	2850	100	80 270 2150	CC-8	▼, ●, ●
30 70 100	5.31	3CONTACT Medium Aluminum	19365	30/100A21/DLSW/2/24 120V	120	24	Soft White	2400	2850	100	270 830 1100	CC-8	▼, ●, ●
			19380	30/100A21/DLSW/RP 120V	120	12	Soft White	2400	2850	100	270 830 1100	CC-8	▼, ●, ●
			19385	30/100A21/W/RP 120V	120	12	Soft White	1200	2850	100	290 915 1205	CC-8	▼, ●, ●
50 200 250	5.31	3CONTACT Medium Aluminum	19404	50/250A21/W/RP 120V	120	12	Soft White	1200	2850	100	580 3300 3880	CC-8	▼, ●, ●
50 100 150	5.31	3CONTACT Medium Aluminum	18044	50/150A21/DLSW/RP 120V	120	12	Soft White	2400	2850	100	510 1280 1790	CC-8	▼, ●, ●
			18458	50/150A21/W/2PK/12 120V	120	12	Soft White	1200	2850	100	580 1540 2120	CC-8	▼, ●, ●
			18060	50/150A21/W/RP 120V	120	12	Soft White	1200	2850	100	580 1540 2120	CC-8	▼, ●, ●

Specifications subject to change without notice.

Notes on page 53