



**Product Number:** 15581

**Order Abbreviation:** 202PS25/CL 125V

**General Description:** Incandescent PS25 Bulb Shape Street Lighting Lamp Clear Finish Medium Brass Base 202Watt 125Volt

Product Information	
Abbrev. With Packaging Info.	202PS25CL 125V 60/CS 1/SKU
Approx. Lumens	2750
Average Rated Life (hr)	6000
Base	Medium Brass
Bulb	PS25
Class	C (gas)
Color Rendering Index (CRI)	100
Color Temperature/CCT (K)	2850
Diameter (in)	3.125
Diameter (mm)	79.38
Filament	C-9
Lamp Finish	Clear
Light Center Length - LCL (in)	5.250
Light Center Length - LCL (mm)	133
Maximum Overall Length - MOL (in)	6.938
Maximum Overall Length - MOL (mm)	176.2125
Nominal Voltage (V)	125.00
Nominal Wattage (W)	202.00