



A21 Med



PS25



PS30



PS35

GENERAL PURPOSE INCANDESCENT LAMPS (cont.)**Incandescent A-Line Lamps for General Illumination, Task and Accent Lighting (cont.)****3-WAY Incandescent Lamps (cont.)**

Nominal Wattage	MDL (in)	Base	Product Number	Ordering Abbreviation	Voltage	Pkg Qty	Finish	Average Rated Life (hrs)	CCT (K)	CRI	Lumens	Filament	Notes
50 100 150	5.31	3CONTACT Medium Aluminum	18110	50/150/DAY/1/12 120V	120	12	Daylight	1200	2900	100	460 1170 1630	CC-8	▼,●,▲
			18167	50/150A21/DLSW/2/24 120V	120	24	Soft White	2400	2850	100	510 1280 1790	CC-8	▼,●,▲
100 200 300	6.94	3CONTACT Mogul	15845	100/300PS25/1/6/RP 120V	120	6	Inside Frost	1200	2850	100	1385 3540 4925	CC-8	▼,●,▲

Incandescent PS25 Lamps

Nominal Wattage	MDL (in)	Base	Product Number	Ordering Abbreviation	Voltage	Pkg Qty	Finish	Average Rated Life (hrs)	CCT (K)	CRI	Lumens	Filament	Notes
150	6.94	Medium Brass	15293	150PS25/SL 120V	120	60	Safeline	1000	2850	100	2200	C-9	●,▲,10
150	5.94	Medium Brass	15300	150PS25/RS/SL 120V	120	60	Safeline	1000	2850	100	2145	C-17	●,▲,10
200	6.94	Medium Brass	15818	200PS25/99/XL 130V	130	60	Inside Frost	2500	2850	100	3000	CC-6	●,▲
202	6.94	Medium Brass	15581	202PS25/CL 125V	125	60	Clear	6000	2850	100	2750	C-9	●,▲

Incandescent PS30 & PS35 Lamps

Nominal Wattage	MDL (in)	Base	Product Number	Ordering Abbreviation	Voltage	Pkg Qty	Finish	Average Rated Life (hrs)	CCT (K)	CRI	Lumens	Filament	Notes
200	8.06	Medium Brass	15725	200PS/CL/99/XL 130V	130	60	Clear	2500	2850	100	2875	C-9	●,▲
200	8.06	Medium	15653	200PS/IF 130V	130	60	Inside Frost	750	2850	100	3560	C-9	●,▲,▲
			15675	200PS/23 130V	130	60	Inside Frost	1000	2850	100	3080	C-9	●,▲,▲
200	8.06	Medium Brass	15648	200PS/SL 120V	120	60	Safeline	1000	2850	100	3080	C-9	●,▲
300	8.06	Medium	15740	300M/CL/RP 120V	120	12	Clear	750	2850	100	5870	C-9	●,▲,▲
			15742	300M/CL 120V	120	60	Clear	750	2850	100	5870	C-9	●,▲,▲
			15744	300M/CL 130V	130	60	Clear	750	2850	100	5820	C-9	●,▲,▲
			15735	300M/IF/RP 120V	120	12	Inside Frost	750	2850	100	5860	C-9	●,▲,▲
			15737	300M/IF 120V	120	60	Inside Frost	750	2850	100	5860	C-9	●,▲,▲
			15738	300M/IF/CVP/6 130V	130	6	Inside Frost	750	2850	100	5760	C-9	●,▲,▲
			15739	300M/IF 130V	130	60	Inside Frost	750	2850	100	5760	C-9	●,▲,▲
300	8.06	Medium Brass	15761	300M/IF/99/XL 130V	130	60	Inside Frost	2500	2850	100	4990	C-9	●,▲,▲
300	9.38	Mogul	15915	300PS35/CL 120V	120	24	Clear	1000	2850	100	5700	C-9	●,▲,▲
			15917	300PS35/CL 130V	130	24	Clear	1000	2850	100	5250	C-9	●,▲,▲
			16068	300PS35/CL 277V	277	24	Clear	1000	2850	100	4220	C-7A	●,▲,▲
			15918	300PS35/IF 120V	120	24	Inside Frost	1000	2850	100	5700	C-9	●,▲,▲
			15920	300PS35/IF 130V	130	24	Inside Frost	1000	2850	100	5250	C-9	●,▲,▲
500	9.38	Mogul	16034	500PS35/CL 130V	130	24	Clear	1000	2850	100	10000	CC-8	●,▲,▲
			16040	500PS35/IF 130V	130	24	Inside Frost	1000	2850	100	10000	CC-8	●,▲,▲

For the current listing of available products and more complete product information, please visit us at www.sylvania.com.