



**Product Number:** 16068

**Order Abbreviation:** 300PS35/CL 277V

**General Description:** Incandescent PS35 Bulb Shape Clear Finish Mogul Base 300Watt 277Volt

Product Information	
Abbrev. With Packaging Info.	300PS35CL 277V 24/CS 1/SKU
Approx. Lumens	4220
Average Rated Life (hr)	1000
Base	Mogul
Bulb	PS35
Class	C (gas)
Color Rendering Index (CRI)	100
Color Temperature/CCT (K)	2850
Diameter (in)	4.375
Diameter (mm)	111.13
Filament	C-7A
Lamp Finish	Clear
Light Center Length - LCL (in)	7.000
Light Center Length - LCL (mm)	178
Maximum Overall Length - MOL (in)	9.375
Maximum Overall Length - MOL (mm)	238.125
Nominal Voltage (V)	277.00
Nominal Wattage (W)	300.00