

Product Number: 16597

Order Abbreviation: 39PAR38/HAL/S/NFL25/TL 120V

General Description: Tungsten Halogen PAR38 Silver Reflector Lamp 39Watt 120Volt Medium Skirted Base NarrowFlood25 Beam Triple Life

Product Information	
Abbrev. With Packaging Info.	39PAR38HALSNFL25TL 120V 10/CS 1/SKU
Approx. Lumens	530
Average Rated Life (hr)	4500
Base	E26 Medium Skirted
Beam Angle (deg)	25
Beam Type	NFL
Bulb	PAR38
Centerbeam Candlepower (cp)	2100
Class	C (gas)
Color Rendering Index (CRI)	99
Color Temperature/CCT (K)	2750
Diameter (in)	4.752
Diameter (mm)	120.70
Ecologic	Yes
Family Brand Name	CAPSYLITE® PAR38
Filament	CC-8
Horizontal Beam Angle (deg)	25
Lamp Finish	Reflector
Maximum Overall Length - MOL (in)	5.313
Maximum Overall Length - MOL (mm)	134.9375
Nominal Voltage (V)	120.00
Nominal Wattage (W)	39.00
Vertical Beam Angle (deg)	25