

**Product Number:** 24308

**Order Abbreviation:** FB34T12/941/6/SS/ECO/UPC

**General Description:** 34W, T12 CURVALUME rapid start SUPERSAVER fluorescent lamp, 6in leg spacing, Rare Earth Phosphor, 4100K color temperature, 90 CRI, UPC. VIVID Color: High CRI lamps for color critical applications.

Product Information	
Abbrev. With Packaging Info.	FB34T129416SSECOUPC 12/CS 1/SKU
Average Rated Life (hr)	20000
Base	Medium Bipin
Bulb	T12
Color Rendering Index (CRI)	90
Color Temperature/CCT (K)	4100
Family Brand Name	Curvalume® SuperSaver®
Initial Lumens at 25C	2650
Nominal Wattage (W)	34.00