

**Product Number:** 24965

**Order Abbreviation:** FB34T129306SSECOUPC

**General Description:** 34W, T12 Curvalume rapid start fluorescent lamp, 6in leg spacing, 3000K color temperature, 90 CRI. VIVID Color: High CRI lamps for color critical applications.

Product Information	
Abbrev. With Packaging Info.	FB34T129306SSECOUPC 12/CS 1/SKU
Average Rated Life (hr)	18000
Base	Medium Bipin
Bulb	T12
Color Rendering Index (CRI)	90
Color Temperature/CCT (K)	3000
Initial Lumens at 25C	2600
Nominal Wattage (W)	34.00