



A19

HALOGEN

GENERAL PURPOSE HALOGEN LAMPS

Halogen A-line Lamps – DOUBLElife™ (120V)

Nominal Wattage	Bulb Shape	MOL (#)	Base	Product Number	Ordering Abbreviation	Finish	Pkg Qty	Average Rated Life (hrs)	Initial Lumens	CCT (K)	CRI	Filament	Life in Years ¹	Cost per Year ²	Notes
28	A19	4.38	E26 Medium	50047	28A19/HAL/DLMS/SW/4 120V	Soft White	48	2000	340	2700	100	CC-8	1.8	\$3.37	5,6,7
43	A19	4.38	E26 Medium	50046	43A19/HAL/DLMS/SW/4 120V	Soft White	48	2000	610	2750	100	CC-8	1.8	\$5.18	5,6,7
				52581	43A/HAL/DLMSSW/8 120V	Soft White	96	2000	610	2750	100	CC-8	1.8	\$5.18	5,6,7
				52634	43A/HAL/DLMS/RP4 144	Soft White	144	2000	610	2750	100	CC-8	1.8	\$5.18	5,6,7
53	A19	4.38	E26 Medium	50045	53A19/HAL/DLMS/SW/4 120V	Soft White	48	2000	800	2775	100	CC-8	1.8	\$6.38	5,6,7
				52626	53A/HAL/DLMS/SW/8 120V	Soft White	96	2000	800	2775	100	CC-8	1.8	\$6.38	5,6,7
72	A19	4.38	E26 Medium	50044	72A19/HAL/DLMS/SW/4 120V	Soft White	48	2000	1150	2800	100	CC-8	1.8	\$8.67	5,6,7
				52582	72A/HAL/DLMSSW/8 120V	Soft White	96	2000	1150	2800	100	CC-8	1.8	\$8.67	5,6,7
				52636	72A/HAL/DLMS/RP4 144	Soft White	144	2000	1150	2800	100	CC-8	1.8	\$8.67	5,6,7

Halogen A-line Lamps – Single Life Modified Spectrum (120V)

Nominal Wattage	Bulb Shape	MOL (#)	Base	Product Number	Ordering Abbreviation	Finish	Pkg Qty	Average Rated Life (hrs)	Initial Lumens	CCT (K)	CRI	Filament	Life in Years ¹	Cost per Year ²	Notes
28/29	A19	4.38	E26 Medium	19008	28A/HAL/SSW/2 120V	Super Soft	24	1000	400	2700	99	CC-8	0.9	\$3.37	5,6,7
				52190	28A/HAL/SSW/4 120V	Super Soft	48	1000	400	2700	99	CC-8	0.9	\$3.37	5,6,7
				52619	29A/HAL/SW/EXTRA4	Extra Soft	48	1000	400	2700	99	CC-8	0.9	\$3.49	5,6,7
43	A19	4.38	E26 Medium	19009	43A/HAL/SSW/2 120V	Super Soft	24	1000	600	2750	99	CC-8	0.9	\$5.18	5,6,7
				50005	43A/HAL/SSW/4 120V	Super Soft	48	1000	600	2750	99	CC-8	0.9	\$5.18	5,6,7
				52611	43A/HAL/SSW/8 120V	Super Soft	96	1000	600	2750	99	CC-8	0.9	\$5.18	5,6,7
				52631	43A/HAL/SSW/RP4/144 120V	Super Soft	144	1000	600	2750	99	CC-8	0.9	\$5.18	5,6,7
				52620	43A/HAL/SW/EXTRA4	Extra Soft	48	1000	600	2750	99	CC-8	0.9	\$5.18	5,6,7
				52637	43A/HAL/MSSW/CVP/16PK	Extra Soft	16	1000	600	2750	99	CC-8	0.9	\$5.18	5,6,7
				52554	53A/HAL/SSW/2 120V	Super Soft	24	1000	850	2775	99	CC-8	0.9	\$6.38	5,6,7
53	A19	4.38	E26 Medium	50018	53A/HAL/SSW/4 120V	Super Soft	48	1000	850	2775	99	CC-8	0.9	\$6.38	5,6,7
				52632	53A/HAL/SSW/RP4/144 120V	Super Soft	144	1000	850	2775	99	CC-8	0.9	\$6.38	5,6,7
				52621	53A/HAL/SW/EXTRA4	Extra Soft	48	1000	850	2775	99	CC-8	0.9	\$6.38	5,6,7
				19010	72A/HAL/SSW/2 120V	Super Soft	24	1000	1200	2800	99	CC-8	0.9	\$8.67	5,6,7
72	A19	4.38	E26 Medium	50006	72A/HAL/SSW/4 120V	Super Soft	48	1000	1200	2800	99	CC-8	0.9	\$8.67	5,6,7
				52633	72A/HAL/SSW/RP4/144 120V	Super Soft	96	1000	1200	2800	99	CC-8	0.9	\$8.67	5,6,7
				52612	72A/HAL/SSW/8 120V	Super Soft	144	1000	1200	2800	99	CC-8	0.9	\$8.67	5,6,7
				52622	72A/HAL/SW/EXTRA4	Extra Soft	48	1000	1200	2800	99	CC-8	0.9	\$8.67	5,6,7

Halogen A-line Lamps – Single Life (120V)

Nominal Wattage	Bulb Shape	MOL (#)	Base	Product Number	Ordering Abbreviation	Finish	Pkg Qty	Average Rated Life (hrs)	Initial Lumens	CCT (K)	CRI	Filament	Life in Years ¹	Cost per Year ²	Notes
28	A19	4.38	E26 Medium	52194	28A/HAL/SW4 120V	Soft White	48	1000	430	2850	100	CC-8	0.9	\$3.37	5,6,7
				52549	28A/HAL/CL/2 120V	Clear	24	1000	435	2850	100	CC-8	0.9	\$3.37	5,6,7
43	A19	4.38	E26 Medium	52204	43A/HAL/SW4 120V	Soft White	48	1000	750	2900	100	CC-8	0.9	\$5.18	5,6,7
				52550	43A/HAL/CL/2 120V	Clear	24	1000	765	2900	100	CC-8	0.9	\$5.18	5,6,7
53	A19	4.38	E26 Medium	52213	53A/HAL/SW4 120V	Soft White	48	1000	1050	2950	100	CC-8	0.9	\$6.38	5,6,7
				52555	53A/HAL/CL/2 120V	Clear	24	1000	1050	2950	100	CC-8	0.9	\$6.38	5,6,7
72	A19	4.38	E26 Medium	52258	72A/HAL/SW4 120V	Soft White	48	1000	1490	3000	100	CC-8	0.9	\$8.67	5,6,7
				52551	72A/HAL/CL/2 120V	Clear	24	1000	1520	3000	100	CC-8	0.9	\$8.67	5,6,7

¹ Life in Years based on 3 hours operation per day.

² Cost per Year based on 3 hours per day, \$0.11 per kWh.

For the current listing of available products and more complete product information, please visit us at www.sylvania.com.