



Bi-Pin



HPL



Med Bi-Pin



Med 2-Pin

HALOGEN**SINGLE END**

| ANSI Code | Product Number | Ordering Abbreviation | Color Temp (K) | Watts (W) | Volts (V) | Base | Lumens (lm) | Avg Rated Life (hrs) | Bulb | Pkg Qty | Symbols & Footnotes |
|-----------|----------------|-----------------------|----------------|-----------|-----------|--------------|-------------|----------------------|------|---------|---------------------|
| | 54704 | HPL 750/240/X (UCF) | 3050 | 750 | 240 | Sp Med Bipin | 15600 | 1500 | T6 | 12 | 23 |
| | 58729 | 60T4OCL | 3100 | 60 | 24 | BA15d | 1280 | 500 | T12 | 12 | |
| | 58939 | 220T4Q/2PPF | 3250 | 220 | 22 | GY9.35 | 6200 | 200 | T4 | 12 | |
| | 58941 | 235T4Q/2PPF | 3250 | 235 | 33 | G29.5 | 5800 | 200 | T4 | 12 | |
| | 54256 | 62138 HLX | | 100 | 12 | G6.35 | 2800 | 50 | T3.5 | 40 | 47 |
| | 54245 | 64223 | 2900 | 10 | 6 | G4 | 150 | 300 | T3 | 40 | |
| | 54021 | 64251 HLX | 3200 | 20 | 6 | PG22 | 500 | 100 | T3 | 30 | |
| | 54262 | 64258 HLX | | 20 | 12 | G4 | 350 | 2000 | T3 | 40 | 45 |
| | 54022 | 64260 | 3300 | 30 | 12 | PG22 | 800 | 50 | T3 | 30 | |
| | 54247 | 64261 | 3300 | 30 | 12 | G6.35 | 750 | 50 | T3.5 | 40 | |
| | 54606 | 64265 HLX | 3200 | 30 | 6 | G4 | 765 | 100 | T3 | 40 | |
| | 54258 | 64275 | 3150 | 35 | 6 | G4 | 780 | 50 | T3 | 40 | |
| | 54318 | 64291 XIR 40W | 3100 | 40 | 23 | G6.35 | 1200 | 600 | T4 | 40 | |
| | 54322 | 64292 XIR 150W | 3250 | 150 | 23 | G6.35 | 6000 | 600 | T4 | 40 | |
| | 54001 | 64501 | 3400 | 150 | 115 | GX6.35 | 4500 | 25 | T4 | 25 | |
| | 54354 | 64514 | 3400 | 300 | 120 | GX6.35 | 8100 | 75 | T6 | 12 | 45 |
| | 58524 | 64515 | 3300 | 300 | 230 | GX6.35 | 9600 | 15 | T6 | 12 | 45 |
| | 54356 | 64516 | 3100 | 300 | 230 | GX6.35 | 7400 | 75 | T6 | 12 | 45,86 |
| | 58525 | 64575 | 3400 | 1000 | 230 | GX6.35 | 33000 | 15 | T8 | 12 | |
| | 54607 | 64602 | 3050 | 50 | 12 | G6.35 | 1000 | 1100 | T3.5 | 40 | 45 |
| | 54608 | 64611 HLX | 3250 | 50 | 12 | G6.35 | 1350 | 100 | T3.5 | 40 | 45 |
| | 54032 | 64621 HLX | 3300 | 100 | 12 | PG22 | 2750 | 2000 | T3.5 | 30 | 45 |
| | 54252 | 64638 HLX | 3350 | 100 | 24 | G6.35 | 2900 | 300 | T4 | 40 | |
| | 54320 | 64647 | | 113 | 24 | G6.35 | 3600 | 300 | T4 | 40 | |
| | 54257 | 64650 | 3100 | 50 | 23 | G6.35 | 1000 | 1300 | T4 | 40 | |
| | 54304 | 64654 HLX 24V | | 250 | 24 | GY9.5 | 9000 | 300 | T4 | 12 | 45 |
| | 54273 | 64664 HLX | 3500 | 400 | 36 | G6.35 | 14500 | 150 | T6 | 12 | 45 |
| | 54274 | 64665 HLX | 3400 | 400 | 36 | G6.35 | 400 | 300 | T6 | 12 | 45 |
| | 54323 | 64668 XIR 80W | 3200 | 80 | 22.8 | G6.35 | 3000 | 400 | | 40 | |
| | 54951 | 64672 500W 230V | 2900 | 500 | 230 | GY9.5 | 8500 | 2000 | T7 | 12 | |
| | 54964 | 64672 500W 240V | 2900 | 500 | 240 | GY9.5 | 8500 | 2000 | T7 | 12 | |
| | 54497 | 64678 800W 230V | 3200 | 800 | 230 | G9.5 | 20000 | 250 | T6 | 12 | ⚙️ |
| | 54965 | 64680 500W 230V | 3200 | 500 | 230 | GY9.5 | 14500 | 50 | T7 | 12 | |
| | 54969 | 64680 500W 240V | 3200 | 500 | 240 | GY9.5 | 14500 | 50 | T7 | 12 | |
| | 54701 | 64805 CP/85 (CP/29) | 3200 | 5000 | 230 | G38 | 135000 | 400 | T19 | 1 | 45 |
| | 54793 | JCP 650W/100V | 3250 | 650 | 100 | GY9.5 | 18750 | 100 | T6 | 12 | |
| | 54181 | Med Hal OS03000-U | | 2.5 | 3.5 | Special Mini | | 15 | | 6 | |
| | 54182 | Med Hal OS03100-U | | 2.7 | 3.5 | Special Mini | | 15 | | 6 | |

For the current listing of available products and more complete product information, please visit us at www.sylvania.com