



PAR38



PAR38



AR70

**DIRECTIONAL HALOGEN REFLECTOR LAMPS (cont.)****CAPSYLITE® PAR38 Reflector Lamps – Colored Lamps (120V)**

Nominal Wattage	Bulb Shape	MOL (in)	Base	Product Number	Ordering Abbreviation	Pkg Qty	Average Rated Life (hrs)	Beam Angle	Initial Lumens	CBCP	CCT (K)	CRI	Life in Years <sup>1</sup>	Cost per Year <sup>2</sup>	Notes		
90	PAR38	5.31	E26 Medium Skirted	16660	90PAR38/FL/Y/RP 120V	6	2000	30	Yellow	–	–	–	–	–	★  2,5,6		
				16661	90PAR38/FL/R/RP 120V	6	2000	30	Red	–	–	–	–	–	–	★  2,5,6	
				16662	90PAR38/FL/W/RP 120V	6	2000	30	Amber	–	–	–	–	–	–	–	★  2,5,6
				16663	90PAR38/FL/B/RP 120V	6	2000	30	Blue	–	–	–	–	–	–	–	★  2,5,6
				16665	90PAR38/FL/G/RP 120V	6	2000	30	Green	–	–	–	–	–	–	–	–

**CAPSYLITE PAR36 Halogen Reflector Lamps (12V)**

Nominal Wattage	Bulb Shape	MOL (in)	Base	Product Number	Ordering Abbreviation	Pkg Qty	Average Rated Life (hrs)	Beam Angle	Initial Lumens	CBCP	CCT (K)	CRI	Filament	Notes
36	PAR36	2.75	Screw Terminal	55057	36PAR36/HAL/WFL32/SCR 12V	12	4000	32	7	1000	3000	100	C-8	2,5,6
				55090	36PAR36/HAL/NSP13 12V	12	4000	13	500	3500	3000	100	C-8	2,5,6
				55091	36PAR36/HAL/WFL30 12V	12	4000	30	500	1000	3000	100	C-8	2,5,6
				55100	36PAR36/HAL/NSP5 12V	12	4000	5	500	17000	3000	100	C-8	2,5,6
50	PAR36	2.75	Screw Terminal	55118	50PAR36/HAL/NSP6 12V	12	4000	6	700	25000	3000	100	C-8	2,5,6
				55017	50PAR36/HAL/WFL30 12V	12	4000	30	700	1400	3000	100	C-8	2,5,6

**AR70 & AR111 Halogen Aluminum Reflector Lamps (12V)****AR70 Aluminum Reflector Lamps – UV Filter capsule with axial filament, engineered for precise aiming (12V)**

Nominal Wattage	Bulb Shape	MOL (in)	Base	Product Number	Ordering Abbreviation	Pkg Qty	Average Rated Life (hrs)	Beam Angle	Initial Lumens	CBCP	CCT (K)	CRI	Filament	Notes
20	AR70	1.97	BA15d Double Contact Bayonet	59013	20AR70/SP8 12V	10	3000	8	150	7700	3000	100	C-8	6,7
				59012	20AR70/FL25 12V	10	3000	25	150	900	3000	100	C-8	6,7
50	AR70	1.97	BA15d Double Contact Bayonet	59017	50AR70/SP8 12V	10	3000	8	400	12500	3000	100	C-8	6,7
				59016	50AR70/FL25 12V	10	3000	25	400	2600	3000	100	C-8	6,7

<sup>1</sup> Life in Years based on 3 hours operation per day.<sup>2</sup> Cost per Year based on 3 hours per day, \$0.11 per kWh.For the current listing of available products and more complete product information, please visit us at [www.sylvania.com](http://www.sylvania.com).