



Product Number: 64038

Order Abbreviation: MS400/BU-ONLY/ED37

General Description: 400W high output, position oriented metal halide lamp, clear, base up burn within 15deg

Product Information	
Abbrev. With Packaging Info.	MS400BUONLYED37 6/CS 1/SKU
Average Rated Life - Vertical (hr)	20000
Base	E39 Mogul
Bulb	ED37
Color Rendering Index (CRI)	65
Color Temperature/CCT (K)	4000
Family Brand Name	Super Metalarc®
Lamp Finish	Clear
Nominal Voltage (V)	135.00
Nominal Wattage (W)	400.00