




**Product Number:** 20878

**Order Abbreviation:** CF18DT/E/1N/841/ECO

**General Description:** DULUX 18W triple compact fluorescent amalgam lamp with 4-pin base, 4100K color temperature, 82 CRI, for use with electronic and dimming ballasts, ECOLOGIC

**Price:** 6.28 USD

**Quantity:**  
1 EA

 [Add to Shopping Basket](#)

#### Product Information

Abbrev. With Packaging Info.	CF18DTEIN841ECO 50/CS 1/SKU
Average Rated Life (hr)	12000
Base	GX24Q-2
Bulb	T4
Color Rendering Index (CRI)	82
Color Temperature/CCT (K)	4100
Diameter (in)	0.000
Diameter (mm)	0.00
Family Brand Name	Dulux® T/E
Industry Standards	IEC 60901- 3418
Initial Lumens at 25C	1164
Mean Lumens at 25C	1001
Maximum Overall Length - MOL (in)	4.4
Maximum Overall Length - MOL (mm)	111
NEMA Generic Designation (old)	CFM18W/GX24Q/841
Nominal Wattage (W)	18.00