



Product Number: 23014

Order Abbreviation: F18T8CW/K24

General Description: 18W, 24" MOL, T8 preheat fluorescent lamp, Cool White phosphor, 4200K color temperature, 60 CRI, appliance and vending applications. 7500 Avg rated life at 3 hrs/start

Price: 7.46 USD

Quantity:
1 EA

 [Add to Shopping Basket](#)

Product Information

Abbrev. With Packaging Info.	F18T8CWK24 24/CS 1/SKU
Actual Length (in)	23.780
Actual Length (mm)	604.01
Average Rated Life (hr)	7500
Base	Medium Bipin
Bulb	T8
Color Rendering Index (CRI)	60
Color Temperature/CCT (K)	4200
Diameter (in)	1.094
Diameter (mm)	27.80
Industry Standards	ANSI C78.81 - 2001
Initial Lumens at 25C	1190
Mean Lumens at 25C	1035
Nominal Length (in)	24.000