

**Product** 23014**Number:****Order** F18T8CW/K24**Abbreviation:**

**General Description:** 18W, 24" MOL, T8 preheat fluorescent lamp, Cool White phosphor, 4200K color temperature, 60 CRI, appliance and vending applications. 7500 Avg rated life at 3 hrs/start

### Product Information

Abbrev. With Packaging Info.	F18T8CWK24 24/CS 1/SKU
Actual Length (in)	23.780
Actual Length (mm)	604.01
Average Rated Life (hr)	7500
Base	Medium Bip in
Bulb	T8
Color Rendering Index (CRI)	60
Color Temperature/CCT (K)	4200
Diameter (in)	1.094
Diameter (mm)	27.80
Industry Standards	ANSI C78.81 - 2001
Initial Lumens at 25C	1190
Mean Lumens at 25C	1035
Nominal Length (in)	24.000
Nominal Length (mm)	609.60
Nominal Wattage (W)	18.00

### Footnotes

- Approximate initial lumens after 100 hours operation.
- The life ratings of fluorescent lamps are based on 3 hr. burning cycles under specified conditions and with ballast meeting ANSI specifications. If burning cycle is increased, there will be a corresponding increase in the average hours life.