



Product Number: 26466

Order Abbreviation: F64T6/CW

General Description: 38W, 64" MOL, T6 instant start Slimline fluorescent lamp, Cool White phosphor, 4200K color temperature, 60 CRI

Price: 13.74 USD

Quantity:
EA

 [Add to Shopping Basket](#)

Product Information

Abbrev. With Packaging Info.	F64T6CW 24/CS 1/SKU
Actual Length (in)	62.000
Actual Length (mm)	1574.80
Average Rated Life (hr)	7500
Base	Single Pin
Bulb	T6
Color Rendering Index (CRI)	60
Color Temperature/CCT (K)	4200
Diameter (in)	0.810
Diameter (mm)	20.57
Initial Lumens at 25C	2800
Mean Lumens at 25C	2464
Mean Lumens at 35C	2464
Nominal Length (in)	64.000
Nominal Length (mm)	1625.60