



Product Number: 21547

Order Abbreviation: FO32/741/ECO/SL

General Description: 32W, 48" MOL, T8 OCTRON fluorescent lamp, 4100K color temperature, rare earth phosphor, 75 CRI, suitable for IS or RS operation, ECOLOGIC, SAFELINE shatter-resistant coating to help contain glass and other lamp components should the lamp be broken

Price: 7.80 USD

Quantity:
1 EA

 [Add to Shopping Basket](#)

Product Information

Abbrev. With Packaging Info.	FO32741ECOSL 30/CS 1/SKU
Actual Length (in)	47.780
Actual Length (mm)	1213.61
Average Rated Life (hr)	25000
Base	Medium Bipin
Bulb	T8
Color Rendering Index (CRI)	75
Color Temperature/CCT (K)	4100
Diameter (in)	1.098
Diameter (mm)	27.90
Family Brand Name	OCTRON® SAFELINE ECOLOGIC
Industry Standards	ANSI C78.81-2003
Initial Lumens at 25C	2520
Mean Lumens at 25C	2320
Nominal Length (in)	48.000
Nominal Length (mm)	1219.20