



**Product Number:** 21720

**Order Abbreviation:** FO32/865/XP/ECO

**General Description:** 32W, 48" MOL, T8 OCTRON XP Extended Performance fluorescent lamp, 6500k color temperature rare earth phosphor, 85 CRI, suitable for IS or RS operation, ECOLOGIC.

**Price:** 4.18 USD

**Quantity:**  
 EA

 [Add to Shopping Basket](#)

#### Product Information

Abbrev. With Packaging Info.	FO32865XPECO 30/CS 1/SKU
Actual Length (in)	47.780
Actual Length (mm)	1213.61
Average Rated Life (hr)	40000
Base	Medium Bipin
Bulb	T8
Color Rendering Index (CRI)	85
Color Temperature/CCT (K)	6500
Diameter (in)	1.098
Diameter (mm)	27.90
Family Brand Name	OCTRON® 800 XP®, ECOLOGIC®
Industry Standards	ANSI C78.81 - 2001
Initial Lumens at 25C	2850
Mean Lumens at 25C	2708
Nominal Length (in)	48.000
Nominal Length (mm)	1219.20
Nominal Wattage (W)	32.00
Life at 3 hrs./start on IS ballasts	24000
Life at 12 hrs./start on IS ballasts	40000