



Order Abbreviation: FO32/841/XP/ECO3/SL

General Description: 32W, 48" MOL, T8 OCTRON XP Extended Performance lamp, 4100K color temperature, rare earth phosphor, 85 CRI, suitable for IS or RS operation, ECOLOGIC, SAFELINE shatter-resistant coating to help contain glass and other components should the lamp break

Price: 6.05 USD

Quantity:
1 EA

 [Add to Shopping Basket](#)

Product Information

Abbrev. With Packaging Info.	FO32841XPECO3SL 30/CS 1/SKU
Actual Length (in)	47.780
Actual Length (mm)	1213.61
Average Rated Life (hr)	36000
Base	Medium Bipin
Bulb	T8
Color Rendering Index (CRI)	85
Color Temperature/CCT (K)	4100
Diameter (in)	1.098
Diameter (mm)	27.90
Family Brand Name	OCTRON® 800 XP® SS, ECOLOGIC® SAFELINE
Industry Standards	ANSI C78.81 - 2005
Initial Lumens at 25C	2940
Mean Lumens at 25C	2793
Nominal Length (in)	48.000
Nominal Length (mm)	1219.20
Nominal Wattage (W)	32.00
Life at 3 hrs./start on IS ballasts	24000
Life at 12 hrs./start on IS ballasts	40000
Life at 3 hrs./start on PRS ballasts	40000