



Actual

**Catalog Number:** 2B10PW  
**Product ID:** 7TAH006160R0005  
**UPC Number:** 78378640022  
**Status:** Active

Aluminum Type 2BPW - Two-Bolt Connector with Spacer for Wire Range Main: 1/0-6 - 1/0-2  
 Tap: 1/0 Str-2 Sol. - 1/0 Str.-2 Str., Bolt Size 1/2

- Single-piece construction.
- UL 486A listed for copper conductor only.

### North American Specifications (UNSPSC)

UNSPSC	39121408 Mechanical connectors
IGCC	4541 Mechanical connectors
Brand Name	Blackburn
Type	Two-Bolt Connector
Special Features	Single-piece construction.
Standard	UL E9809
Material	Aluminum
Conductor Range (Main/Primary)	1/0-6 - 1/0-2
Conductor Range (Tap/Secondary)	1/0 Str-2 Sol. - 1/0 Str.-2 Str.
Bolt Size	42737

### European Specifications (ETIM)

ETIM	EC000491 Earth terminal clamp
Suitable for	Round conductor
Material	Aluminium

### Packaging

Inner Quantity	25
Inner Dimensions (inches)	5x3.37x6.5
Outer Quantity	250
Outer Dimensions (inches)	19.4x11.6x5.8
Weight Uom	22 lbs. per 100

### Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)