

Single Speed Fans (On/Off)

WhisperGreen
VENTILATION FAN



FV-05VK3 50 CFM 4" or 6" Duct
FV-08VK3 80 CFM 4" or 6" Duct
FV-11VK3 110 CFM 4" or 6" Duct

WhisperGreen Key Benefits:

- SmartFlow™ technology for optimal CFM output
- Fully enclosed DC motor for long life – rated for 60,000 hours continuous run
- Detachable dual 4" or 6" duct adaptor included
- Fits in 2 x 8 construction

WhisperGreen	FV-05VK3	FV-08VK3	FV-11VK3
Characteristics			
Static pressure in inches w. g.	0.1 0.25	0.1 0.25	0.1 0.25
Air Volume (CFM)	50 54	80 79	110 112
Noise (sones)	<0.3 0.3	<0.3 0.4	0.3 0.8
Power Consumption (Watts)	4.3 7.5	7.0 11.0	11.5 16.2
Energy Efficiency (CFMs/Watt)	12.4 7.7	12.1 7.6	9.7 7.0
Speed	749 1101	832 1130	953 1229
Current	0.05 0.02	0.02 0.01	0.21 0.30
Power Rating (V/Hz)	120/60		



CALGreen



WhisperCeiling
VENTILATION FAN



FV-05VQ5 50 CFM 4" or 6" Duct
FV-08VQ5 80 CFM 4" or 6" Duct
FV-11VQ5 110 CFM 4" or 6" Duct

FV-15VQ5 150 CFM 6" Duct

WhisperCeiling Key Benefits:

- Detachable dual 4" or 6" duct adaptor on 50-110 CFM models
- Fits in 2 x 8 construction

WhisperCeiling	FV-05VQ5	FV-08VQ5	FV-11VQ5	FV-15VQ5
Characteristics				
Static pressure in inches w. g.	0.1 0.25	0.1 0.25	0.1 0.25	0.1 0.25
Air Volume (CFM)	50 36	80 62	110 91	150 127
Noise (sones)	<0.3 0.5	<0.3 0.4	<0.3 0.5	<0.3 0.5
Power Consumption (Watts)	11.0 11.5	14.7 14.5	21.1 20.7	28.4 27.3
Energy Efficiency (CFMs/Watt)	4.7 3.2	5.8 4.5	5.3 4.5	5.3 4.7
Speed	731 1060	829 1089	950 1161	691 911
Current	0.09 0.10	0.12 0.12	0.18 0.17	0.24 0.23
Power Rating (V/Hz)	120/60			



CALGreen



WhisperFit
VENTILATION FAN



INCLUDED:
4 to 3 inch adaptor

FV-05VF2 50 CFM 4" or 3" Duct
FV-08VF2 80 CFM 4" or 3" Duct
FV-11VF2 110 CFM 4" or 3" Duct

WhisperFit Key Benefits:

- Low profile housing design – Ideal for remodeling!
- Fits in 2 x 6 & 2 x 8 construction

WhisperFit	FV-05VF2		FV-08VF2		FV-11VF2	
Characteristics	4" Duct	3" Duct	4" Duct	3" Duct	4" Duct	3" Duct
Static pressure in inches w. g.	0.1 0.25	0.1 0.25	0.1 0.25	0.1 0.25	0.1 0.25	0.1 0.25
Air Volume (CFM)	50 30	50 31	80 60	70 53	110 94	90 78
Noise (sones)	0.4 0.9	0.5 1.1	0.8 1.0	0.8 1.1	1.5 1.5	1.5 2.0
Power Consumption (Watts)	15.0 14.7	15.0 14.8	24.5 24.3	24.3 24.0	33.5 33.2	33.8 33.5
Energy Efficiency (CFMs/Watt)	3.3 2.0	3.3 2.1	3.3 2.5	2.9 2.2	3.3 2.8	2.7 2.3
Speed	637 932	741 978	757 956	845 1007	830 1000	1029 1128
Current	0.13 0.12	0.13 0.12	0.20 0.20	0.20 0.20	0.28 0.28	0.28 0.28
Power Rating (V/Hz)	120/60		120/60		120/60	



CALGreen



WhisperValue
VENTILATION FAN



WhisperValue U-Can Contractor Pack

The Contractor Pack includes four complete fans. The housing and motor/grille are packaged separately for flexibility during installation.

Universal Housing Can	Motor/Grille Assembly	Complete Fan Unit	Master Pack
FV-05-08VSA1	FV-05VSB1	FV-05VS1	4
FV-05-08VSA1	FV-08VSB1	FV-08VS1	4
FV-05-08VSA1	FV-10VSB1	FV-10VS1	4

FV-05VS1 50 CFM 4" Oval Duct
FV-08VS1 80 CFM 4" Oval Duct
FV-10VS1 100 CFM 4" Oval Duct

WhisperValue Key Benefits:

- Super low profile housing design
- UL listed for wall or ceiling installation
- Fits in 2 x 4, 2 x 6 & 2 x 8 construction

WhisperValue	FV-05VS1	FV-08VS1	FV-10VS1
Characteristics	4" Oval Duct	4" Oval Duct	4" Oval Duct
Static pressure in inches w. g.	0.1 0.25	0.1 0.25	0.1 0.25
Air Volume (CFM)	50 37	80 71	100 90
Noise (sones)	0.4 1.0	1.3 1.5	1.5 1.5
Power Consumption (Watts)	18.1 17.8	27.4 27.6	36.4 36.1
Energy Efficiency (CFMs/Watt)	3.2 2.4	3.4 2.8	2.9 2.7
Speed (RPM)	759 948	878 1026	840 979
Current (amps)	0.04 0.04	0.11 0.11	0.30 0.30
Power Rating (V/Hz)	120/60		