

Single Speed Fans with Lights (On/Off)



5-5/8" Depth

(with 3" duct adaptor)



FV-05VFL4 50 CFM 4" or 3" Duct
FV-08VFL4 80 CFM 4" or 3" Duct
FV-11VFL4 110 CFM 4" or 3" Duct



INCLUDED:
4" to 3" adaptor



INCLUDES: (2) 13W ENERGY STAR rated self ballasted GU24 base CFL lamps and a 4W night light. 3500Kelvin/ High CRI/997 Lumens per lamp/75 Lumens Per Watt/10,000 hours, rated average life/equivalent to (2) 75W incandescent lamps.

WhisperFit-Lite Key Benefits:

- Low profile housing design – Ideal for remodeling projects and manufactured structured homes
- Fits in 2 x 6 and 2 x 8 construction
- Detachable 4" to 3" duct adaptor included
- UL listed for tub/shower enclosure when used with a GFCI protected circuit
- Can be used to comply with ASHRAE 62.2, LEED, IAP, California Title 24 and WA Ventilation Code

WhisperFit-Lite Characteristics	FV-05VFL4		FV-08VFL4		FV-11VFL4	
	4" Duct	3" Duct	4" Duct	3" Duct	4" Duct	3" Duct
Static pressure in inches w. g.	0.1	0.25	0.1	0.25	0.1	0.25
Air Volume (CFM)	50	34	50	35	80	67
Noise (sones)	<0.3	0.4	<0.3	0.5	0.5	0.8
Power Consumption (Watts)	14.8	14.7	14.8	14.6	28.4	28.1
Energy Efficiency (CFMs/Watt)	3.6	2.4	3.4	2.4	2.8	2.4
Speed	692	962	747	983	803	1005
Current	0.12	0.12	0.12	0.12	0.24	0.24
Power Rating (V/Hz)	120/60		120/60		120/60	



3-3/8" Depth
Lowest profile, Actually fits in a 2 x 4!

FV-08VSL3 80 CFM 4" Oval Duct
FV-10VSL3 100 CFM 4" Oval Duct

WhisperValue-Lite U-Can Contractor Pack

Universal Housing Can	Motor/Grille Assembly	Complete Fan Unit	Master Pack
FV-08-10VSLA3	FV-08VSLB3	FV-08VSL3	4
FV-08-10VSLA3	FV-10VSLB3	FV-10VSL3	4

The Contractor Pack includes 4 complete fans. The housing and motor/grille are packaged separately for flexibility during installation.

*Must order in quantities of 4, shipment will contain 1 box with 4 units.



WhisperValue-Lite Key Benefits:

- Ideal for residential construction (single and multi-family) and manufactured homes
- 3-3/8" housing depth – lowest profile Energy Star fan available
- L-shaped bracket simplifies installation and provides strong support
- UL approved for ceiling or wall mount – actually fits in a 2 x 4 stud bay
- Wall installation eliminates the need for a radiation damper
- Can be used to comply with ASHRAE 62.2, LEED, IAP, California Title 24 and WA Ventilation Code

WhisperValue-Lite Characteristics	FV-08VSL3		FV-10VSL3	
	4" Oval Duct		4" Oval Duct	
Static pressure in inches w. g.	0.1	0.25	0.1	0.25
Air Volume (CFM)	80	72	100	91
Noise (sones)	1.0	1.2	1.4	1.5
Power Consumption (Watts)	22.5	22.9	30.2	30.3
Energy Efficiency (CFMs/Watt)	3.6	3.1	3.3	3.0
Speed (RPM)	825	1021	918	1087
Current (amps)	0.19	0.19	0.26	0.26
Power Rating (V/Hz)	120/60		120/60	