

# Panasonic



## WhisperGreen-Lite™ 80 CFM Ventilation Fan

Model: FV-08VKL3

Motor Type	DC
Type of Motor Bearing	Ball
Thermal Fuse Protection	Yes
Blower Wheel Type	Sirocco
Duct Diameter (inches)	4" or 6"
Mounting Opening (inches sq.)	10 1/2"
Grille Size (inches sq.)	13"
SmartAction™ Motion Sensor	No
High/Low Delay Timer	No
CustomVent™ Variable	No

Speed Control	
SmartFlow™ Optimum CFM Technology	Yes
Lamp Watts	1 x 32
Lamp Color Rendering Index	84
Color Temperature (Kelvin)	3,500
Rated Life (hours)	10,000
Lamp Model #	LPFHT32E35
Night Light Lamp Watts	4
Washington State VIAQ Code	Yes
California Title 24 Compliant	Yes
Mfg in ISO 9001 Certified Facility	Yes
Energy Star Qualified	Yes
Gross Weight (lbs.)	13.4
UL tub/Shower Enclosure	Yes
Dimensions (H x W x D)	12.0" x 14.25" x 17.0"
Weight	13.5 lbs