

> [WhisperLite](#) > FV-08VQL6

FV-08VQL6

WhisperLite® 80 CFM Ceiling Mounted Fan/Light Combination

See dealer for price



- [Architectural Specs](#)
- [Installation Instructions \(English\)](#)

[Print this page](#)

[View/compare all models](#)

overview

features

support & resources

UPC Code	8 85170 12391 5
Motor Type	AC
Type of Motor Bearing	Ball
Thermal Fuse Protection	Yes
Blower Wheel Type	Sirocco
Mounting Opening (inches sq.)	10 1/2"
Grille Size (inches sq.)	13"
SmartAction Motion Sensor	No
High/Low Delay Timer	No
CustomVent Variable Speed Control	No

Lamp Watts	2x13W
Lamp Color Rendering Index	>80
Color Temperature (Kelvin)	3500K
Rated Life (Hours)	10,000
Lamp Model #	MLS13GU35
Night Light Lamp Watts	4
Washington State VIAQ Code	Yes
California Title 24 Compliant	Yes
Mfg in ISO 9001 Certified Facility	Yes
Duct Diameter (inches)	4" or 6"
Energy Star Qualified	Yes
Gross Weight (lbs.)	12.6
UL tub/Shower Enclosure	Yes
Dimensions (HxWxD)	16.5" x 14.5" x 12.0"

Features, specifications & pricing subject to change without notice.
Copyright © 2009 Panasonic Corporation of North America. All rights reserved.
*** See Online Privacy Policy ***