

A. System Overview

PanTher™ LS8E Hand-Held Thermal Transfer Printer and Accessories

- Cut-to-length functionality eliminates label waste and label trimming labor
- Partial cut feature available to provide tear-apart strips of labels
- P1™ Label Cassette contains an integrated memory device for automatic formatting, recall of last legend used, and number of labels remaining in the cassette
- Market specific labeling tools simplify label creation for electrical components, panel building, and construction and maintenance
- USB interface for importing data, system upgrades, and printing from a wireless laptop or desktop computer
- Prints self-laminating labels, heat shrink tubing, die-cut component labels and continuous tapes
- Fast loading label cassette includes both label material and ribbon to make changing labels easy
- Large graphic display with backlight for improved visibility



LS8E-KIT



LS8EQ

Part Number	Part Description	Std. Pkg. Qty.
LS8EQ-KIT-ACS	Includes LS8EQ printer with QWERTY keypad, one cassette of S100X150VAC self-laminating labels, six AA alkaline batteries, LS8E-ACS, LS8-CASE, LS8-PCKIT, LS8-IB, LS8-WS, quick reference card and operator's manual.	1
LS8EQ-KIT	Includes LS8EQ printer with QWERTY keypad, one cassette of S100X150VAC self-laminating labels, six AA alkaline batteries, LS8-CASE, LS8-PCKIT, LS8-IB, LS8-WS, quick reference card and operator's manual.	1
LS8EQ	Includes LS8EQ printer with QWERTY keypad, one cassette of S100X150VAC self-laminating labels, six AA alkaline batteries and quick reference card.	1
LS8E-KIT-ACS	Includes LS8E printer, one cassette of S100X150VAC self-laminating labels, six AA alkaline batteries, LS8E-ACS, LS8-CASE, LS8-PCKIT, LS8-IB, LS8-WS, quick reference card and operator's manual.	1
LS8E-KIT	Includes LS8E printer, one cassette of S100X150VAC self-laminating labels, six AA alkaline batteries, LS8-CASE, LS8-PCKIT, LS8-IB, LS8-WS, quick reference card and operator's manual.	1
LS8E	Includes LS8E printer, one cassette of S100X150VAC self-laminating labels, six AA alkaline batteries and quick reference card.	1
LS8E-ACS*	120 VAC power adapter for North America.	1
LS8-CASE	Rigid carrying case.	1
LS8-PCKIT	Includes USB cable and PC interface software for importing data, system upgrades, or printing from a wireless laptop or desktop computer.	1
LS8-IB	Protective impact bumper.	1
LS8-WS	Wrist strap.	1
LS8-CLN	LS8/LS8E cleaning kit – contains bottle of cleaning solution with MSDS, cleaning pen, swabs, alcohol wipes and cleaning instructions.	1

*Cannot be used to charge batteries.
Other adapters available, replace S with A (Australia), C (China), E (Europe) and U (UK).

Cougar™ LS9 Hand-Held Thermal Transfer Printer and Accessories

- Economical identification system provides premium quality solutions at the lowest installed cost
- Cut-to-length functionality eliminates label waste and label trimming labor
- Partial cut feature available to provide tear-apart strips of labels
- P1™ Label Cassette contains an integrated memory device for automatic formatting, recall of last legend used, and number of labels remaining in the cassette
- Prints continuous military grade heat shrink tubing
- Prints a wide variety of continuous tapes for marking of wire marking, component labeling, and safety/facility identification
- Fast loading label cassette includes both label material and ribbon to make changing labels easy



LS9Q

Part Number	Part Description	Std. Pkg. Qty.
LS9Q	Includes LS9Q printer with QWERTY keypad, one cassette of T100X000C1C-BK continuous nylon cloth tape, six AA alkaline batteries and quick reference card.	1
LS9	Includes LS9 printer, one cassette of T100X000VPC-BK continuous vinyl tape, six AA alkaline batteries and quick reference card.	1
LS9-ACS*	120 VAC power adapter for North America.	1
LS9-CASE	Rigid carrying case.	1
LS9-IB	Protective impact bumper.	1
LS9-WS	Wrist strap.	1
LS9-CLN	Cleaning kit.	1

*Cannot be used to charge batteries.
Other adapters available, replace S with A (Australia), C (China), E (Europe) and U (UK).

B1. Cable Ties

B2. Cable Accessories

B3. Stainless Steel Ties

C1. Wiring Duct

C2. Surface Raceway

C3. Abrasion Protection

C4. Cable Management

D1. Terminals

D2. Power Connectors

D3. Grounding Connectors

E1. Labeling Systems

E2. Labels

E3. Pre-Printed & Write-On Markers

E4. Permanent Identification

E5. Lockout/Tagout & Safety Solutions

F. Index

PANDUIT® ELECTRICAL SOLUTIONS

A. System Overview	Part Number	Page Number	Part Number	Page Number	Part Number	Page Number
B1. Cable Ties	LCMA16-6-C	D2.108	LCMD35-10-Q	D2.109	LS9-IB	E1.2
	LCMA16-8-C	D2.108	LCMD35-12-Q	D2.109	LS9-WS	E1.2
	LCMA185-10-X	D2.108	LCMD35-8CD-Q	D2.109	LS9Q	E1.2
	LCMA185-12-X	D2.108	LCMD400-00-5	D2.110	LTYK	D3.6
	LCMA185-16-X	D2.108	LCMD400-12-5	D2.110	LV-S-1G	C4.9
B2. Cable Accessories	LCMA185-20-X	D2.108	LCMD400-14-5	D2.110	LV-S-2G	C4.9
	LCMA240-10-X	D2.108	LCMD400-16-5	D2.110	LV-W-1G	C4.9
	LCMA240-12-X	D2.108	LCMD50-00-X	D2.109	LV-W-2G	C4.9
	LCMA240-16-X	D2.108	LCMD50-10-X	D2.109	LWC100-A-L	B2.34
	LCMA240-20-X	D2.108	LCMD50-10CD-X	D2.109	LWC100-A-L14	B2.34
B3. Stainless Steel Ties	LCMA25-10-C	D2.108	LCMD50-12-X	D2.109	LWC100-A-L20	B2.34
	LCMA25-6-C	D2.108	LCMD500-00-1	D2.110	LWC100-H25-L	B2.34
	LCMA25-8-C	D2.108	LCMD500-12-1	D2.110	LWC100-H25-L14	B2.34
	LCMA300-10-5	D2.108	LCMD500-14-1	D2.110	LWC100-H25-L20	B2.34
	LCMA300-12-5	D2.108	LCMD500-16-1	D2.110	LWC19-A-C	B2.34
C1. Wiring Duct	LCMA300-16-5	D2.108	LCMD6-5CD-Q	D2.109	LWC19-A-C14	B2.34
	LCMA300-20-5	D2.108	LCMD630-00-1	D2.110	LWC19-A-C20	B2.34
	LCMA35-10-C	D2.108	LCMD630-12-1	D2.110	LWC19-A-C25	B2.34
	LCMA35-12-C	D2.108	LCMD630-14-1	D2.110	LWC19-H25-C14	B2.34
	LCMA35-6-C	D2.108	LCMD630-16-1	D2.110	LWC25-A-C	B2.34
C2. Surface Raceway	LCMA35-8-C	D2.108	LCMD70-00-X	D2.109	LWC25-A-C14	B2.34
	LCMA400-12-5	D2.108	LCMD70-10-X	D2.109	LWC25-A-C20	B2.34
	LCMA400-16-5	D2.108	LCMD70-10CD-X	D2.109	LWC25-H25-C	B2.34
	LCMA400-20-5	D2.108	LCMD70-12-X	D2.109	LWC25-H25-C14	B2.34
	LCMA50-10-L	D2.108	LCMD95-00-X	D2.109	LWC25-H25-C20	B2.34
C3. Abrasion Protection	LCMA50-12-L	D2.108	LCMD95-10CD-X	D2.109	LWC38-A-C	B2.34
	LCMA50-6-L	D2.108	LCMD95-12-X	D2.109	LWC38-A-C14	B2.34
	LCMA50-8-L	D2.108	LCMD95-14-X	D2.109	LWC38-A-C20	B2.34
	LCMA500-00-1	D2.108	LD10IW10-A	C2.58	LWC38-H25-C	B2.34
	LCMA500-12-1	D2.108	LD10IW6-A	C2.58	LWC38-H25-C14	B2.34
C4. Cable Management	LCMA500-16-1	D2.108	LD10IW8-A	C2.58	LWC38-H25-C20	B2.34
	LCMA500-20-1	D2.108	LD2P10IW10-A	C2.57	LWC50-A-L	B2.34
	LCMA6-5-C	D2.107	LD2P10IW8-A	C2.57	LWC50-A-L14	B2.34
	LCMA6-6-C	D2.107	LD3IW10-A	C2.58	LWC50-A-L20	B2.34
	LCMA6-8-C	D2.107	LD3IW6-A	C2.58	LWC50-H25-L	B2.34
D1. Terminals	LCMA630-00-1	D2.108	LD3IW8-A	C2.58	LWC50-H25-L14	B2.34
	LCMA630-16-1	D2.108	LD5IW10-A	C2.58	LWC50-H25-L20	B2.34
	LCMA630-20-1	D2.108	LD5IW6-A	C2.58	LWC75-A-L	B2.34
	LCMA70-10-L	D2.108	LD5IW8-A	C2.58	LWC75-A-L14	B2.34
	LCMA70-12-L	D2.108	LDPH10IW10-A	C2.59	LWC75-A-L20	B2.34
D2. Power Connectors	LCMA70-6-L	D2.108	LDPH10IW8-A	C2.59	LWC75-H25-L	B2.34
	LCMA70-8-L	D2.108	LDPH3IW10-A	C2.59	LWC75-H25-L14	B2.34
	LCMA95-10-L	D2.108	LDPH3IW8-A	C2.59	LWC75-H25-L20	B2.34
	LCMA95-12-L	D2.108	LDPH5IW10-A	C2.59		
	LCMA95-16-L	D2.108	LDPH5IW8-A	C2.59		
D3. Grounding Connectors	LCMA95-8-L	D2.108	LDS3IW10-A	C2.60		
	LCMD10-00-Q	D2.109	LDS5IW10-A	C2.60	M200X050Y6T	E2.10
	LCMD10-6CD-Q	D2.109	LHMS-S10-D	B2.17	M200X050Y7T	E2.10
	LCMD10-8-Q	D2.109	LHMS-S5-D	B2.17	M200X100Y6T	E2.10
	LCMD120-00-X	D2.110	LHMS-S6-D	B2.17	M200X100Y7T	E2.10
E1. Labeling Systems	LCMD120-10CD-X	D2.110	LI-112S-L	D3.24	M300X050Y6C	E1.7
	LCMD120-12-X	D2.110	LI-252S-Q	D3.24	M300X050Y6T	E2.10
	LCMD120-14-X	D2.110	LI-50S-C	D3.24	M300X050Y7C	E1.7
	LCMD150-00-X	D2.110	LMD3IW-Q	C2.60	M300X050Y7T	E2.10
	LCMD150-10CD-X	D2.110	LMD5IW-Q	C2.60	M300X100Y6T	E2.10
E2. Labels	LCMD150-12-X	D2.110	LPFCM14-A-C14	B2.37	M300X100Y7T	E2.10
	LCMD150-14-X	D2.110	LPFCM22-A-C14	B2.37	MACC25-A-C	B2.33
	LCMD16-00-Q	D2.109	LPFCM34-A-C14	B2.37	MACC25-AV-D	B2.33
	LCMD16-6CD-Q	D2.109	LPMM-S2-C	B2.14	MACC62-A-C	B2.33
	LCMD16-8-Q	D2.109	LPMM-S5-C	B2.14	MACC62-AV-C	B2.33
E3. Pre-Printed & Write-On Markers	LCMD185-00-X	D2.110	LPMS-S8-C	B2.14	MBCEH-QR316	B3.13
	LCMD185-10CD-X	D2.110	LS8-CASE	E1.2	MBCH-QR316	B3.13
	LCMD185-12-X	D2.110	LS8-CLN	E1.2	MBCSH-QR316	B3.13
	LCMD185-14-X	D2.110	LS8-IB	E1.2	MBEH-TLR	B3.12
	LCMD240-00-5	D2.110	LS8-PCKIT	E1.2	MBEH-TLR316	B3.12
E4. Permanent Identification	LCMD240-10CD-5	D2.110	LS8-WS	E1.2	MBH-TLR316	B3.12
	LCMD240-12-5	D2.110	LS8E	E1.2	MBH-MR	B3.12
	LCMD240-14-5	D2.110	LS8E-ACS	E1.2	MBH-MR316	B3.12
	LCMD25-00-Q	D2.109	LS8E-KIT	E1.2	MBH-TLR	B3.12
	LCMD25-10-Q	D2.109	LS8E-KIT-ACS	E1.2	MBH-TLR316	B3.12
E5. Lockout/Tagout & Safety Solutions	LCMD25-12-Q	D2.109	LS8EQ	E1.2	MBM-H25-Q	B3.28
	LCMD25-8-Q	D2.109	LS8EQ-KIT	E1.2	MBMS-S10-CY	B2.19
	LCMD25-8CD-Q	D2.109	LS8EQ-KIT-ACS	E1.2	MBS-MR	B3.12
	LCMD300-00-5	D2.110	LS9	E1.2	MBS-MR316	B3.12
	LCMD300-12-5	D2.110	LS9-ACS	E1.2	MBS-TLR	B3.12
F. Index	LCMD300-14-5	D2.110	LS9-CASE	E1.2	MBS-TLR316	B3.12
	LCMD35-00-Q	D2.109	LS9-CLN	E1.2	MBSH-TR	B3.12

M