

| PANDUIT PART NUMBER | STUD SIZE | DIMENSIONS in. | | | | |
|---------------------|-----------|----------------|---------------|---------------|---------------|---------------|
| | | A $\pm.03$ | W $\pm.01$ | C MIN | M $\pm.03$ | H $\pm.01$ |
| P18-4R | #4 | .62 (15.8) | .25 (6.4) | .21 (5.3) | .50 (12.7) | .12 (3.1) |
| P18-6RN | #6 | .60 (15.2) | .22 (5.6) | .19 (4.8) | .49 (12.5) | .15 (3.8) |
| P18-6R | #6 | .62 (15.8) | .25 (6.4) | .21 (5.3) | .50 (12.7) | .15 (3.8) |
| P18-8R | #8 | .71 (18.0) | .31 (7.9) | .25 (6.4) | .55 (14.0) | .17 (4.3) |
| P18-10R | #10 | .71 (18.0) | .31 (7.9) | .25 (6.4) | .55 (14.0) | .20 (5.1) |
| P18-14R | 1/4" | .91 (23.1) | .46 (11.7) | .38 (9.7) | .68 (17.3) | .27 (6.9) |
| P18-56R | 5/16" | .91 (23.1) | .46 (11.7) | .38 (9.7) | .68 (17.3) | .34 (8.6) |
| P18-38R | 3/8" | 1.00 (25.4) | .53 (13.5) | .43 (10.9) | .73 (18.5) | .40 (10.2) |
| P18-12R | 1/2" | 1.20 (30.5) | .72 (18.3) | .53 (13.5) | .84 (21.3) | .52 (13.2) |



NOTES:

- UL LISTED AND CSA CERTIFIED FOR:
 - #22-16 AWG SOLID OR STRANDED COPPER WIRE
 - 302° F (150° C) MAX. TEMP. RATING
- MATERIAL:
 - STAMPING - .03" (.8) THK COPPER, TIN PLATED
- SEE www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
- DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
- INSTALLATION TOOLS:
 - UL LISTED AND CSA CERTIFIED: CT-100, CT-100A, CT-200, CT-570, CT-600-A, CT-1570, CT-2500
 - PANDUIT APPROVED: CT-160, CT-260
- WIRE STRIP LENGTH: $9/32^{+1/32}_0$ (7.1 $^{+.8}_0$)



LISTED
587H
E52164



CERTIFIED
LR31212

| REV | DATE | BY | DESCRIPTION | CUST | PM |
|-----|------|------|--|------|-----|
| 07 | 8/11 | SHOR | MODIFIED NOTE #3, ADDED INSTALLATION TOOLS, REMOVED QUANTITIES | | |
| 06 | 5/02 | SRB | CHANGED (DIMS) TO 1 PL DECIMAL | | |
| 05 | 4/02 | SRB | ADDED P18-12R | | TRO |

PANDUIT CORP.

TINLEY PARK, ILLINOIS

#22-18 BARREL NON-INSULATED RING TONGUE

| | | | |
|-----------------|--------------|---------------|-----------------------|
| DRAWN BY DAW | CHK'D RLS | SCALE NONE | DRAWING NO. A41263 |
|-----------------|--------------|---------------|-----------------------|