



Search Panduit.com



Search within category

BUY NOW

DESIGN / INSTALL

CSA Certified	Yes
UL Listed	Yes
Length (In.)	0.90
Length (mm)	22.9
Width (In.)	0.31
Width (mm)	7.9
CE Compliant	No
Clearance	0.23
Clearance (mm)	5.8
Insulation	Vinyl
Max. Ins.	0.170
Max. Ins. (mm)	4.3
Panduit Color Code	Blue
Part Features	Fast and Easy Installation, Insulation Support, Brazed Seam protects terminal barrel from splitting during crimping process, Internal Barrel Serrations assure good wire contact and maximum tensile strength
Plating Type	Tinned
Stock	0.03
Stock (mm)	0.8
Stud Size	#8
Tool	CT-100A , CT-600-A , CT-1550 , CT-1551 , CT-2500
Wire Range	16 - 14 AWG
Wire Range (mm²)	1.5 - 2.5
RoHS Compliancy Status	Compliant
Min. Order Qty.	20.0000