



Search within category

BUY NOW

DESIGN / INSTALL



PV14-8LF-E

Locking Fork Terminal, vinyl insulated, funnel entry, 18 – 14 AWG, #8 stud size, convenience package.

Specs Packaging Details Tools [★ Add to Favorites](#) [Add to BOM](#)

Documents

Stud Size In. (mm)	#8 (M4)
Style	Locking Fork
Wire Range In. (mm ²)	18 - 14 AWG (1.0 - 2.5)
Barrel Configuration	Funnel Entry
Barrel Type	Brazed seam with Insulation Support
Base Material	Copper
Insulation	Vinyl
Panduit Color Code	Blue
Plating Type	Tinned
Part Number Series	PV-LF
Max. Ins.	0.17
Max. Ins. (mm)	4.3
Stock	0.03
Stock (mm)	0.76
Width In (mm)	0.29 (7.4)
Wire Strip Length In. (mm)	5/16" (.3125) - (7.9)
Flammability Rating	UL 94V-0
Max. Voltage Rating	600 V
CA-800/EZ Series Crimp Die	-
CA9 Series Crimp Die	-
Tool	CT-100A , CT-600 , CT-1550 , CT-1551 , CT-2500
CSA Certified	C22.2 No.65
Standards	American Bureau of Shipping (ABS)
UL Listed	UL486A-486B
Packaging Type	Bag
Pieces Per Reel	-
Part Features	• Locks in place for secure connection • Fork design provides for fast and easy

installation, without the need to remove fastener • Insulation support helps to prevent wire damage in bending applications • Internal barrel serrations assure good wire contact and maximum tensile strength

RoHS Compliancy Status Compliant

Min. Order Qty. 20.0000

[LEGAL INFORMATION](#) | [PRIVACY POLICY](#) | [CONTACT US](#) | [SITE MAP](#) | [WHERE TO BUY](#) | [JOBS](#) | [UNSUBSCRIBE](#)