



SOLUTIONS

PRODUCTS AND SERVICES

SUPPORT

ABOUT US

Search Panduit.com



Search within category

BUY NOW

DESIGN / INSTALL

**PUR6004BU-W**

The copper cable is enhanced Category 6 (riser CMR) U/UTP, 4-pair with conductors that are 23 AWG construction with polyethylene insulation. The cable is twisted in pairs, separated by an integrated pair divider, and protected by a flame-retardant PVC jacket. It is packaged in an easy-payout carton. It is blue and 1000' (305m) long.

Specs

Packaging Details

Documents

★ Add to Favorites

🛒 Add to BOM

AWG Size	23
Length (ft.)	1000
Length (m)	305
Nominal Diameter (In.)	0.231
Nominal Diameter (mm)	5.8
Jacket Material	CMR – Flame-retardant PVC
No. of Pairs	4
Packaging Type	Easy-payout carton
CE Compliant	No
Application	Ethernet 10BASE-T, 100BASE-T (Fast Ethernet), 1000BASE-T (Gigabit Ethernet), 10GBASE-T (10 Gigabit Ethernet over limited distances as specified in the industry 10GBASE-T standards), 155 Mb/s ATM, 622 Mb/s ATM, 1.2 Gb/s ATM, Token Ring 4/16
Cable Type	U/UTP
Color	Blue
Flammability Rating	Riser - UL1666 CSA FT-4
Insulation	Polyolefin
Nominal Cable O.D. (In.)	0.231
Nominal Cable O.D. (mm)	5.8
Part Features	Third party tested, Integrated pair divider and Reelex™ packaging
Performance Level	Category 6/Class E
Weight (Kg)	11.4/305m
Weight (lbs)	25/1000 ft.
RoHS Compliancy Status	Compliant
Min. Order Qty.	12,000.0000