



D278

GE DC Motor, Kinamatic,
5BPA56NAG10A, .75HP, 1725 RPM,
180VDC

Small DC Motors - Motors

GE DC Motor, Kinamatic, Type-K Power
Supply, 5BPA56NAG10A, 3/4HP, 1725
RPM, 180VDC, 56C Frame, Bolt on
Base, Totally Enclosed, Permanent
Magnet, End Mounted

Weight: 45 lbs

Obsolete Parts this Product

Replaces: 5BPA56NAG10A