



Actual

Catalog Number: ADR60-22D
Product ID: 7TAH006600R0237
UPC Number: 78378661034
EAN Number: 05415022398250
Status: Active

Type ADR-ALCUL Two-Conductor, Two-Hole Mount, Conductor Range 2 Str-600 kcmil, Length 5-5/16 Inches, Width 2-3/4 Inches, Height 1-1/2 Inches, 1/2 Inch Bolt Hole, 1-3/4 Inch Centers, Tin Plated

- Easy Installation - no special tools required.

North American Specifications (UNSPSC)

UNSPSC	39121408 Mechanical connectors
IGCC	4541 Mechanical connectors
Brand Name	Blackburn
Type	Dual-Rated Mechanical Connector
Special Features	Easy Installation - no special tools required.
Standard	UL E9809
Number Of Conductors	2
Material	Aluminum
Finish	Tin-Plated
Conductor Range (Main/Primary)	2-600
Number Of Mounting Holes	2
Mounting Hole Spacing	1/2 Inch

Packaging

Inner Quantity	3
Inner Dimensions (inches)	9.8x4.1x2.3
Outer Quantity	30
Outer Dimensions (inches)	11.2x8.8x17.2
Weight Uom	80 lbs. per 100

Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-000390

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com